

SPECIFICATIONS

ELECTRICAL

FREQUENCY: 0-18 GHZ
 IMPEDANCE: 50 OHMS
 VSWR: 1.15:1 MAX @ 18 GHZ
 VRMS 500 V SEA LEVEL

MECHANICAL



MATERIALS BODY PASS STAINLESS STEEL
 CONTACT PLATING: Au PER MIL-G-45204
 DIELECTRIC: TEFLON
 INTERFACE: MIL-STD-348A
 DURABILITY: 500 CYCLES MIN

ENVIRONMENTAL

OPERATING TEMPERATURE: -65°C TO 165°C

CORROSION MIL-STD-202
 VIBRATION MIL-STD-202
 SHOCK MIL-STD-202

ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

2.92mm-N ADAPTERS S STEEL 18 GHZ

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM3125, SM3130, SM3135, SM3140	--

SCALE SHEET