

SMA F/F ADAPTERS NO EPOXY HOLE

SM4932

SPECIFICATIONS

ELECTRICAL

50 OHMS

VSWR 1.20:1 MAX @ 18 GHZ

FREQUENCY: 0-18 GHZ

MECHANICAL

500 CYCLES MIN

7-10 LBS COUPLING NUT MATING TORQUE

ENVIRONMENTAL


-65 DEG C TO +85 DEG C

MATERIALS BODY PASSIVATED STAINLESS STEEL

CENTER CONTACTS BECU

CONTACT PLATING: Au PER MIL-G-45204

ROHS COMPLIANT



NO EPOXY HOLE FOR IMPROVED EMI PERFORMANCE

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA F/F ADAPTERS NO EPOXY HOLE

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SM4932	C

SCALE

SHEET