


REVISION				
ZONE	REV.	DESCRIPTION	DATE	CHANGED BY
A		INITIAL RELEASE	01/31/2023	HBAKKE
				AGANMANI



- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT:  
36 INCHES OR LESS, ONE LABEL APPROXIMATELY  
CENTERED. LONGER THAN 36 INCHES, TWO LABELS  
APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
  - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

**Fairview Microwave®**  
an INFINITT® brand

Website: [www.FairviewMicrowave.com](http://www.FairviewMicrowave.com)  
Phone: 1.800.715.4396 | 1.972.649.6678

INTERPRET ALL DIMENSIONS AND  
TOLERANCES PER ASME Y14.5

SCALE NONE SHEET 1 OF 1

DESCRIPTION  
SHV PLUG RIGHT ANGLE TO SHV JACK CABLE USING RG58  
COAX

UNLESS OTHERWISE SPECIFIED  
LEADING DIMENSIONS ARE INCHES  
DIMENSIONS IN [ ] ARE MILLIMETERS

TOLERANCES:

X = ± .2	[ .5 ]	FRACTIONS
.XX = ± .02	[ .5 ]	± 1/32
XXX = ± .005	[ .13 ]	ANGLES ± 1°

CABLE LENGTH TOLERANCES:

≤ 12 [305]	± .1 [25]	/ -0
> 12 [305] ≤ 60 [1524]	± .2 [51]	/ -0
> 60 [1524] ≤ 120 [3048]	± .4 [102]	/ -0
> 120 [3048] ≤ 300 [7620]	± .6 [152]	/ -0
> 300 [7620]	± .5%	/ -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY  
AND SUBJECT TO CHANGE WITHOUT NOTICE

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV
A	3FKR5	HBAKKE	FMCA3143	A

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.  
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE  
EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.