



REVISION				
ZONE	REV	DESCRIPTION	DATE	CHANGED BY
	A	INITIAL RELEASE	04/19/2023	VTHANGARAJ
				APPROVED
				AGANWANI



- NOTES:
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		<div><div><div></div><div></div><div></div><div></div></div><div><div></div><div></div><div></div><div></div></div></div> <div>Fairview Microwave® an INFINITI® brand</div>		<div></div> <div>INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5</div>	
TOLERANCES:		SCALE		SHEET	
.X = ± .2	[.5]	FRACTIONS		NONE	
.XX = ± .02	[.13]	± 1/32		1 OF 1	
XXX = ± .005	[.13]	ANGLES ± 1°			
CABLE LENGTH TOLERANCES:					
≤ 12 [305] = ± 1 [25] / -0					
> 12 [305] ≤ 60 [1524] = ± 2 [51] / -0					
> 60 [1524] ≤ 120 [3048] = ± 4 [102] / -0					
> 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0					
> 300 [7620] = ± 5% / -0					
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE		DESCRIPTION		REV	
SIZE		DRAWN BY		A	
A		VTHANGARAJ		FMCA3167	
CAGE CODE		ITEM NO.		A	
3FKR5		LMR-100-FR Coax			
		Fire Rated BNC Male to BNC Male Low Loss Cable Using			