




NOTES:

1. FEMALE CONTACT ACCEPTS PIN SIZE $\phi .009$ [0.23] $\nabla .071$ [1.80] MAX.
2. SEPARATE METAL CONTACT RING (PASSIVATED).

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = ± 2 [5]	FRACTIONS $\pm 1/32$
XX = ± 0.02 [0.5]	ANGLES $\pm 1^\circ$
XXX = ± 0.005 [0.13]	
CABLE LENGTH TOLERANCES:	
≤ 12 [305] = ± 1 [25] / -0	
> 12 [305] ≤ 60 [1524] = ± 2 [51] / -0	
> 60 [1524] ≤ 120 [3048] = ± 4 [102] / -0	
> 120 [3048] ≤ 300 [7620] = ± 6 [152] / -0	
> 300 [7620] = $\pm 5\%$ / -0	
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE UN-DIMENSIONED/NON-CRITICAL FEATURES MAY VARY IN SIZE AND LOCATION COLORS MAY VARY	

Fairview Microwave® an INFINIT® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
Website: www.FairviewMicrowave.com Phone: 1.800.715.4396 1.972.649.6678		SCALE NONE	SHEET 1 OF 1
DESCRIPTION			
1.85mm FEMALE CONNECTOR FIELD REPLACEABLE ATTACHMENT 2 HOLE FLANGE WITH EMI GASKET, ACCEPTS 0.51mm (.020inch) PIN			
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	MVEERAPPAN	FMCN1809
			REV
			B