



REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	4/8/2020	S.PONG



LABEL:

FAIRVIEW MICROWAVE
FMCP1108
D/C: YYYY

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.



TITLE			
SIZE	CAGE CODE	DRAWN BY	ITEM NO.
A	3FKR5	K.Dang	FMCP1108
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.			
SCALE			
N/A			
REV			
A			

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES

DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

X = ±.2	[5.08]	FRACTIONS	L ≤ 12 [305] = ±.1 [25] / -0
XX = ±.02	[.51]	± 1/32	12 [305] < L ≤ 60 [1524] = ±.2 [51] / -0
XXX = ±.005	[.13]	ANGLES ± 1°	60 [1524] < L ≤ 120 [3048] = ±.4 [102] / -0
			120 [3048] < L ≤ 300 [7620] = +.6 [152] / -0
			300 [7620] < L = +5% / -0

CABLE LENGTH (L) TOLERANCES:

L ≤ 12 [305]	= ±.1 [25] / -0
12 [305] < L ≤ 60 [1524]	= ±.2 [51] / -0
60 [1524] < L ≤ 120 [3048]	= ±.4 [102] / -0
120 [3048] < L ≤ 300 [7620]	= +.6 [152] / -0
300 [7620] < L	= +5% / -0



THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF FAIRVIEW MICROWAVE CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1