


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	B	ECO-12727	07/20/2023	LNAGARAJ	WILLIAMSON



NOTES:

1. LABEL FOR REFERENCE ONLY.
LABEL LOCATION FOR REFERENCE ONLY.
2. MOUNTING BRACKET INCLUDED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = ±.2	[5]	FRACTIONS
.XX = ±.02	[.5]	± 1/32
.XXX = ±.005	[.13]	ANGLES ± 1°


CABLE LENGTH TOLERANCES:

$$\begin{aligned} &\leq 12 \text{ [305]} = +1 \text{ [25]} / -0 \\ &> 12 \text{ [305]} \leq 60 \text{ [1524]} = +2 \text{ [51]} / -0 \\ &> 60 \text{ [1524]} \leq 120 \text{ [3048]} = +4 \text{ [102]} / -0 \\ &> 120 \text{ [3048]} \leq 300 \text{ [7620]} = +6 \text{ [152]} / -0 \\ &> 300 \text{ [7620]} = +5\% / -0 \end{aligned}$$

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.



Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE

SHEET
1 OF 1

DESCRIPTION

BROADBAND GAIN HORN ANTENNA, 6 GHZ TO 67 GHZ
13 DBI GAIN, 1.85MM FEMALE CONNECTOR

SIZE	A
------	---

E	CAGE CODE 3FKR5
---	--------------------

DRAWN BY	KGL
----------	-----

ITEM NO.	DESCRIPTION	QTY	UNIT	AMOUNT
----------	-------------	-----	------	--------

FMWAN1160

REV
B