

FMC2122085 DATA SHEET

RA SMP Female to SMP Female Cable FM-F086 Coax

Electrical Specifications

Description	Min	Тур	Max	Units			
Frequency Range	DC		18	GHz			
VSWR		1.35:1					
Velocity of Propagation		70.6		%			
Capacitance	28	3.95 [94.9	pF/ft [pF/m]				

Mechanical Specifications

Cable Assembly

Weight 0.00132 lbs [0.6 g]

Cable

Cable Type FM-F086
Impedance 50 Ohms
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Silver

Dielectric Type PTFE

Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter

2 Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Blue

0.104 in [2.64 mm]

Connectors

Connector 1	Connector 2	
SMP Female	SMP Female	
Standard	Standard	
50 Ohms	50 Ohms	
Beryllium Copper, Gold	Beryllium Copper, Gold	
MIL-G-45204	30µ in. minimum	
PTFE	PTFE	
Beryllium Copper, Gold	Beryllium Copper, Gold	
MIL-G-45204	30µ in. minimum	
	SMP Female Standard 50 Ohms Beryllium Copper, Gold MIL-G-45204 PTFE Beryllium Copper, Gold	

Environmental Specifications

Temperature

Operating Range -65 to +165 deg C

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:



Configuration:

- SMP Female Right Angle
- SMP Female
- FM-F086

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013


Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





Typical Performance Data



RA SMP Female to SMP Female Cable FM-F086 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: RA SMP Female to SMP Female Cable FM-F086 Coax FMC2122085


URL: http://www.fairviewmicrowave.com/ra-smp-female-smp-female-cable-hs086-coax-fmc2122085-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

FMC2122085-12 = 12 inches long cable FMC2122085-100cm = 100 cm long cable







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RA SMP Female to SMP Female Cable FM-F086 Coax	DWG NO FMC2122085			CAGE CODE 3FKR5		
	CAD FILE 103114	SHEET	SCALE N/A	SIZE A	5568	