



# RA SMA Female to SMA Female 4 Hole Flange **Adapter**

RA SMA female to SMA female 4 hole flange adapter part number SM5277 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA adapter has a female to female gender configuration. SM5277 SMA female to SMA female adapter operates to 14 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. This low profile right angle SMA adapter allows for easier connections in tight spaces. Our RF SMA to SMA 4 hole flange adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connnector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

# **Electrical Specifications**

| Description            | Min   | Тур | Max   | Units |
|------------------------|-------|-----|-------|-------|
| Frequency Range        | DC    |     | 14    | GHz   |
| VSWR                   |       |     | 1.2:1 |       |
| Operating Voltage (AC) |       |     | 500   | Vrms  |
| DWV (AC)               |       |     | 1,500 | Vrms  |
| Insulation Resistance  | 5,000 |     |       | MOhms |

**Electrical Specification Notes:** Values at 25° C, sea level.

#### **Mechanical Specifications**

**Size** Lenath

1.05 in [26.67 mm] Width 0.5 in [12.7 mm] Weight

0.01411 lbs [6.4 g]

| Description                | Connector 1 | Connector 2 |  |  |
|----------------------------|-------------|-------------|--|--|
| Туре                       | SMA Female  | SMA Female  |  |  |
| Polarity                   | Standard    | Standard    |  |  |
| Interface Specification    | MIL-STD-348 | MIL-STD-348 |  |  |
| Contact Captivation Method | Epoxy       | Ероху       |  |  |
| Mating Cycles              | 500         | 500         |  |  |



# **Configuration:**

- SMA Female Connector 1
- SMA Female Connector 2
- 50 Ohms
- Right Angle Body Geometry
- 4 Hole Flange Mount Method

#### **Features:**

- VSWR of 1.2:1 max up to 14 GHz
- SMA interface meets MIL-STD-348
- Epoxy captivation
- Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

# **Applications:**

- General Purpose Test
- Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Material Specifications**

| Description            | Connector 1                | Connector 2                |
|------------------------|----------------------------|----------------------------|
| Туре                   | SMA Female                 | SMA Female                 |
| Contact Material       | Beryllium Copper           | Beryllium Copper           |
| Contact Plating        | Gold                       | Gold                       |
| Contact Plating Spec.  | MIL-G-45204                | MIL-G-45204                |
| Insulation Material    | PTFE                       | PTFE                       |
| Outer Contact Material | Passivated Stainless Steel | Passivated Stainless Steel |

## **Environmental Specifications**

**Temperature** 

Operating Range


-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

## **Typical Performance Data**







RA SMA Female to SMA Female 4 Hole Flange Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RA SMA Female to SMA Female 4 Hole Flange Adapter SM5277

URL: https://www.fairviewmicrowave.com/ra-sma-female-sma-female-4-hole-flange-adapter-sm5277-p.aspx









| FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM | NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm]. |       |      |                 |        |      |
|---|---|-------|------|-----------------|--------|------|
| RA SMA Female to SMA Female 4 Hole Flange Adapter                 | DWG NO SM5277   |       |      | CAGE CODE 3FKR5 |        |      |
|   | CAD FILE 081315   | SHEET | SCAL | E N/A           | SIZE A | 5568 |