

# Miter RA SMA Female to 2.92mm Female Adapter with Passivated Stainless Steel Body, DC to 27 GHz

Miter RA SMA female to 2.92mm female adapter part number FMAD1565 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to 2.92mm adapter has a female to female gender configuration and is built of durable stainless steel. FMAD1565 SMA female to 2.92mm female adapter operates to 27 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. This miter right angle SMA to 2.92mm adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

## **Electrical Specifications**

Description	Min	Тур	Мах	Units
Frequency Range	DC		27	GHz
VSWR			1.2:1	

## **Mechanical Specifications**

<b>Size</b> Length Width Height Weight		0.600 in [15.2 mm] 0.26 in [6.6 mm] 0.63 in [16 mm] 0.023 lbs [10.43 g]
Description	Connector 1	Connector 2
Туре	SMA Female	2.92mm Female
Polarity	Standard	Standard
Mating Cycles	500	500

### **Material Specifications**

Description	Connector 1	Connector 2	
Туре	SMA Female	2.92mm Female	
Contact Material	Beryllium Copper	Beryllium Copper	
Contact Plating	Gold over Nickel	Gold over Nickel	
Insulation Material	Oxide-Noryl	Oxide-Noryl	
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel	
Body Material	Passivated Stainless Steel	Passivated Stainless Steel	





# **Configuration:**

- SMA Female Connector 1
- 2.92mm Female Connector 2
- •50 Ohm
- Miter Right Angle Body Geometry

## **Features:**

- VSWR of 1.2:1 max up to 27 GHz
- Gold over Nickel Plated
  Beryllium Copper Contact

# **Applications:**

- Enables Between Series
  Connections
- General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**


Notes:

Miter RA SMA Female to 2.92mm Female Adapter with Passivated Stainless Steel Body, DC to 27 GHz from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Miter RA SMA Female to 2.92mm Female Adapter with Passivated Stainless Steel Body, DC to 27 GHz FMAD1565

URL: https://www.fairviewmicrowave.com/sma-female-2.92-female-right-angle-adapter-fmad1565-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689