

SMA/M-MMCX/M FLEXIBLE CABLES RG316

FMC0209316-XX

SPECIFICATIONS

CABLE ASSEMBLY:

VSWR:1.2:1 @ < 3GHZ TYPICAL

RAW CABLE: RG316

TYPICAL LOSS (EXCLUDING CONNECTORS)

@ 100MHZ: 0.08 DB/FT

@ 1GHZ: 0.26 DB/FT

@ 2GHZ: 0.38 DB/FT

@ 3GHZ: 0.47 DB/FT

CONNECTORS: BRASS


SMA Torque 5-in-lbs

CONTACTS Au PLATING 30uin

INTERFACE: MIL-STD-348A

OP TEMP: -55-110°C

ROHS COMPLIANT



FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

SMA/M-MMCX/M FLEXIBLE CABLES RG316

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	FMC0209316-XX	--
SCALE		SHEET	

ALL DIMENSIONS IN inches(MM) Typical