



# QMA Male Connector Crimp/Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100

QMA male connector with crimp/solder attachment for RG174, RG316, RG188, .100 inch and LMR-100, part number FMCN1892, from Fairview Microwave is instock and ships same day. This QMA male connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.12:1.

Fairview's QMA male connector FMCN1892 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

# **Electrical Specifications**

| Description     | Min | Тур | Max    | Units |
|-----------------|-----|-----|--------|-------|
| Frequency Range | DC  |     | 6      | GHz   |
| VSWR            |     |     | 1.12:1 |       |

## **Performance by Frequency**

| Description | F1      | F2     | F3 | F4 | F5 | Units |
|-------------|---------|--------|----|----|----|-------|
| Freq. Range | DC to 3 | 3 to 6 |    |    |    | GHz   |
| VSWR, Max   | 1.05:1  | 1.12:1 |    |    |    |       |

**Electrical Specification Notes:** 

Connector is optimized up to 6 GHz.

#### **Mechanical Specifications**

Size

Length 1.02 in [25.91 mm]
Width/Dia. 0.41 in [10.41 mm]
Height 0.5 in [12.7 mm]
Weight 0.014 lbs [6.35 g]

Mating Cycles 100 Cycles

#### **Material Specifications**

| 0.11      |  |
|-----------|--|
| Gold      |  |
|           |  |
| Tri-Metal |  |
| Tri-Metal |  |
|           |  |



# **Configuration:**

- QMA Male Connector
- 50 Ohms
- Straight Body Geometry
- RG174, RG316, RG188, .100 inch, LMR-100 Interface Type
- Crimp/Solder Attachment

### **Features:**

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.12:1
- · Gold Plated Brass Contact

# **Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





# **Environmental Specifications Temperature**

Operating Range

-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

QMA Male Connector Crimp/Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100 from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: QMA Male Connector Crimp/Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100 FMCN1892

URL: https://www.fairviewmicrowave.com/gma-male-rg174-rg316-rg188-.100-lmr-100-connector-fmcn1892-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





