an INFINIT® brand

QMA Female Bulkhead Mount Connector Crimp/ Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100, .268 inch D Hole

QMA female bulkhead connector with crimp/solder attachment for RG174, RG316, RG188, .100 inch and LMR-100 (.268 inch D hole), part number FMCN1895, from Fairview Microwave is in-stock and ships same day. This QMA female connector operates up to a maximum frequency of 18 GHz. Fairview's FMCN1895 bulkhead QMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's QMA female bulkhead connector FMCN1895 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

| Description | Min | Тур | Max | Units |
|---------------------------|-------|-----|-----|-------|
| Frequency Range | DC | | 18 | GHz |
| Operating Voltage (AC) | | | 350 | Vrms |
| Test Voltage (AC) | | | 750 | Vrms |
| Inner Cond. DC Resistance | e | | 3 | mOhms |
| Outer Cond. DC Resistanc | е | | 2.5 | mOhms |
| Insulation Resistance | 5,000 | | | MOhms |
| Insulation Resistance | 5,000 | | | IVIO |

Performance by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-------------|---------|--------|----|----|----|-------|
| Freq. Range | DC to 3 | 3 to 6 | | | | GHz |
| VSWR, Max | 1.07:1 | 1.11:1 | | | | |

Electrical Specification Notes:

RF leakage: 95 dB (up to 2 GHz), 80 dB (up to 4 GHz), 70 dB (up to 6 GHz) min.

Insertion loss = 0.05 x sqrt(fGHz) dB max up to 6 GHz.

Mechanical Specifications

| Size | |
|---------------|--------------------|
| Length | 0.95 in [24.13 mm] |
| Width/Dia. | 0.43 in [10.92 mm] |
| Height | 0.5 in [12.7 mm] |
| Weight | 0.012 lbs [5.44 g] |
| Mating Cycles | 100 Cycles |

Material Specifications

| Description | Material | Plating |
|-------------|------------------|---------|
| Contact | Beryllium Copper | Gold |



FMCN1895

DATA SHEET

Configuration:

- QMA Female Connector
- 50 Ohms
- Straight Body Geometry
- RG174, RG316, RG188, .100 inch, LMR-100 Interface Type
- Crimp/Solder Attachment
- Bulkhead

Features:

- Operating Frequency of 18 GHz Max.
- Gold Plated Beryllium Copper Contact

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT[©] brand



| Insulation | PTFE | |
|------------|-------|-----------|
| Body | Brass | Tri-Metal |

Environmental Specifications

| Temperature | |
|-----------------|------------------------------|
| Operating Range | -40 to +85 deg C |
| Storage Range | -40 to +85 deg C |
| Humidity | IEC 60169-1 16.3 (96 hours) |
| Vibration | IEC 60068-2-64 random |
| Thermal Shock | IEC 60169-1 16.4 (-40/+85°C) |
| Salt Spray | IEC 60109-1 16.7 (48 hrs) |

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

QMA Female Bulkhead Mount Connector Crimp/Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100, .268 inch D Hole from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: QMA Female Bulkhead Mount Connector Crimp/ Solder Attachment for RG174, RG316, RG188, 0.100 inch, LMR-100, .268 inch D Hole FMCN1895


URL: https://www.fairviewmicrowave.com/qma-female-rg174-rg316-rg188-.100-Imr-100-connector-fmcn1895-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

Fairview Microwave







301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689