



# SMA 180 Degree Hybrid Coupler from 1.4 GHz to 6 GHz Rated to 30 Watts

The FMCP1154 is a high power 180 degree hybrid coupler that operates from 1.4 to 6 GHz and can handle 30 Watts (CW) with 22 dB isolation minimum and 1.3:1 VSWR maximum. The package interface uses SMA Female connectors.

The FMCP1154 is part of Fairview Microwave's family of 180 degree hybrid couplers that offer excellent performance featuring high isolation, low insertion loss and VSWR while maintaining great amplitude/phase balance over the entire operating frequency range. They are available in both narrow and broad bandwidths and can be used in a wide variety of applications including signal sampling, phased array radar, and any application that requires even power distribution with a 180 degree difference in phase.



Description	Min	Тур	Max	Units
Frequency Range	1.4		6	GHz
Impedance		50		Ohms
Phase Difference		180		Degrees
Coupling		3		dB
Insertion Loss		1.2	1.8	dB
Isolation	22	30		dB
VSWR		1.2:1	1.3:1	
Amplitude Balance		±0.4	±0.1	dB
Phase Balance		5	7	Degrees
Input Power (CW)			30	Watts
Input Power (Peak)			300	Watts



#### Features:

- 180° Phase Shift Between Output Ports
- High power handling of 30 Watts CW
- 1.4 to 6 GHz Frequency Range
- VSWR 1.2:1 Typical
- High Isolation of 22 dB Minimum
- Low 1.2 dB Insertion Loss Typical
- SMA Female Connectors
- Stable performance over Operating Temperature Range

# **Applications:**

- · Test and Measurement
- Commerical Communications
- SATCOM
- Military Communications
- Wireless Communications

# **Mechanical Specifications**

#### Size

Length Width Height Weight 4.14 in [105.16 mm] 2.05 in [52.07 mm] 0.43 in [10.92 mm] 0.25 lbs [113.4 g]

Configuration

RF Connector Type

SMA Female

# **Environmental Specifications**

Temperature

Operating Range Storage Range

Humidity

Shock

Vibration

Altitude

-45 to +85 deg C -55 to +125 deg C

100% RH at 35°c, 95% RH at 40°c

20G for 11msec half sine wave, 3 axis both directions

25gRMS (15 degrees 2KHz) endurance, 1 hour per axis

30,000 ft.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






## **Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**


Notes:

#### **Typical Performance Data**









SMA 180 Degree Hybrid Coupler from 1.4 GHz to 6 GHz Rated to 30 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SMA 180 Degree Hybrid Coupler from 1.4 GHz to 6 GHz Rated to 30 Watts FMCP1154

URL: https://www.fairviewmicrowave.com/sma-180-degree-hybrid-coupler-1.4-6-ghz-30-watts-fmcp1154-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





