

4 Way Power Divider SMA Connectors From 15 GHz to 26.5 GHz Rated at 20 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, 2.4mm, 1.85mm BNC, N and SMA.

The FMDV1146 is a 4-way power divider that operates from 15 to 26.5 GHz and can handle up to 20 Watts (CW) with 1.2 dB max insertion loss and 16 dB min isolation. The package interface uses SMA female connectors.

Electrical Specifications

Number of Output Ports				4
Description	Min	Typ	Max	Units
Frequency Range	15		26.5	GHz
Impedance		50		Ohms
Input VSWR		1.55:1	1.7:1	
Output VSWR		1.4:1	1.6:1	
Insertion Loss		0.7	1.2	dB
Isolation	16	18		dB
Amplitude Balance		0.3	0.4	dB
Phase Balance		3	5	Degrees
Nominal Power Splitting		6		dB
Input Power (CW)				20 Watts
Reverse Power (CW)				0.5 Watts
Input Power (Peak) 10% Duty Cycle 1us Pulse Width				200 Watts

Mechanical Specifications

Size	
Length	2.03 in [51.56 mm]
Width	1.37 in [34.8 mm]
Height	0.39 in [9.91 mm]
Weight	0.144 lbs [65.32 g]
Housing Material and Plating	Aluminum
Configuration	
Package Type	Connectorized
Input Connector	SMA Female
Output Connectors	SMA Female

Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C



Features:

- 4-Way Power Divider
- SMA Female Connectorized Design
- 15 to 26.5 GHz Frequency Range
- Max Power 20 Watts (CW)
- Insertion Loss < 1.2 dB
- Isolation > 16 dB

Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Humidity	100% RH at 35°C, 95%RH at 40°C
Shock	20G for 11msec half sine wave, 3 axis both directions
Vibration	25gRMS (15 degrees 2KHz) endurance, 1 hour per axis
Altitude	30,000 ft. (Epoxy Sealed Controlled environment)

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4 Way Power Divider SMA Connectors From 15 GHz to 26.5 GHz Rated at 20 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [4 Way Power Divider SMA Connectors From 15 GHz to 26.5 GHz Rated at 20 Watts FMDV1146](#)

URL: <https://www.fairviewmicrowave.com/4-way-power-divider-sma-26.5-ghz-fmdv1146-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

