

## 8 way Power Divider SMA Connectors from 500 MHz to 1000 MHz Rated at 30 Watts

Fairview Microwave carries a wide selection of power dividers to fit your needs. These components are essential in many systems, allowing the combination of multiple signals or splitting of a single signal into multiple signals with equal magnitude and phase. Fairview Microwave's resistive and Wilkinson power dividers come with excellent performance featuring minimal loss, high isolation and low VSWR. They are available in both narrow and broad bandwidths with a variety of connector types such as 2.92mm, BNC, N and SMA.

The FMDV1212 is a 8-way power divider that operates from 500 to 1000 MHz and can handle up to 30 Watts (CW) with 0.7 dB max insertion loss and 20 dB min isolation. The package interface uses SMA female connectors.

### Electrical Specifications


Number of Output Ports				8
Description	Min	Typ	Max	Units
Frequency Range	500		1,000	MHz
Impedance		50		Ohms
Input VSWR		1.3:1	1.35:1	
Output VSWR		1.2:1	1.25:1	
Insertion Loss		0.5	0.7	dB
Isolation	20	23		dB
Amplitude Balance		0.25	0.45	dB
Phase Balance		3	5	Degrees
Nominal Power Splitting		9		dB
Input Power (CW)				30 Watts

### Mechanical Specifications

<b>Size</b>	
Length	4.446 in [112.93 mm]
Width	3.12 in [79.25 mm]
Height	0.507 in [12.88 mm]
Weight	1.69 lbs [766.57 g]
Housing Material and Plating	Aluminum
<b>Configuration</b>	
Input Connector	SMA Female
Output Connectors	SMA Female

### Environmental Specifications

<b>Temperature</b>	
Operating Range	-40 to +85 deg C
Storage Range	-50 to +105 deg C
Humidity	100% RH at 35°C, 95%RH at 40°C



### Features:

- 8-Way Power Divider
- SMA Female Connectorized Design
- 500 to 1000 MHz Frequency Range
- Max Power 30 Watts (CW)
- Insertion Loss < 0.7 dB
- Isolation > 20 dB

### Applications:

- Test and Measurement
- Military Communications
- Commercial Communications
- Wireless Communications
- SATCOM

Fairview Microwave  
 301 Leora Ln., Suite 100  
 Lewisville, TX 75056  
 Tel: 1-800-715-4396 / (972) 649-6678  
 Fax: (972) 649-6689  
[www.fairviewmicrowave.com](http://www.fairviewmicrowave.com)  
[sales@fairviewmicrowave.com](mailto:sales@fairviewmicrowave.com)

Shock  
Vibration  
Altitude

20G for 11msec half sine wave, 3 axis both directions  
25g RMS (15 degrees 2KHz) endurance, 1 hour per axis  
30,000 ft.

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

8 way Power Divider SMA Connectors from 500 MHz to 1000 MHz Rated at 30 Watts from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [8 way Power Divider SMA Connectors from 500 MHz to 1000 MHz Rated at 30 Watts FMDV1212](#)

URL: <https://www.fairviewmicrowave.com/8-way-power-divider-1-mhz-fmdv1212-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

