

BNC PCB RECEPTACLE

SC6215


SPECIFICATIONS

ELECTRICAL:

FREQUENCY: 0-4 GHZ
IMPEDANCE: 50 OHMS

MECHANICAL:

MATERIAL BODY: Ni PLATED BRASS
CENTER CONTACT: BeCu
CONTACT PLATING: Au MIL-G-45204
CAPTIVATED CONTACT
INSULATOR: TEFLON
INTERFACE: MIL-STD-883A
ROHS COMPLIANT
OP. TEMP RANGE: -55°C to +155°C



.063" MAX BOARD THICKNESS

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

TITLE

BNC PCB RECEPTACLE

SIZE	CAGE CODE	DWG NO	REV
A	3FKR5	SC6215	
SCALE	SHEET		