

FMC0716315 DATA SHEET

MCX Plug (Male) to SMB Plug (Male) Cable RG-316 Coax Up To 3 GHz, 1.35 VSWR

The MCX plug to SMB plug cable using RG-316 coax, part number FMC0716315, from Fairview Microwave is in-stock and ships same day. This Fairview MCX to SMB cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC0716315 MCX plug to SMB plug cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Ty	/p Max	Units
Frequency Range	DC		3	GHz
VSWR			1.35:1	
Velocity of Propagation		7	0	%
Capacitance		32 [1)4.99]	pF/ft [pF/m]

Mechanical Specifications

Cable Assembly Weight		0.00838 lbs [3.8 g]	
Cable Cable Type Impedance Inner Conductor Type Inner Conductor Mater Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter	ial and Plating	RG-316 50 Ohms Solid Copper, Silver PTFE 1 Silver Plated Copper Tape Silver Plated Copper Braid FEP, Black 0.098 in [2.49 mm]	

Connectors

Description	Connector 1	Connector 2
Туре	MCX Plug	SMB Plug
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Spec.	30µ" Min	30µ in. minimum
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Gold	Brass, Gold
Body Plating Spec.	3µ" Minimum	3µ in. minimum

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Configuration:

- MCX Plug
- SMB Plug
- RG-316

Features:

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

Applications:

- General Purpose
- Laboratory Use





Environmental Specifications

Temperature Operating Range

-65 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data Notes:

How to Order

Part Numb	er Configura	tion:	F	MC0716315	-	XX	uu	
	-						I	cm = Centimeters <blank> = Inches Length</blank>
Example:		15-12 = 12 inches 15-100cm = 100 cr						

MCX Plug (Male) to SMB Plug (Male) Cable RG-316 Coax Up To 3 GHz, 1.35 VSWR from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.


Click the following link to obtain additional part information: MCX Plug (Male) to SMB Plug (Male) Cable RG-316 Coax Up To 3 GHz, 1.35 VSWR FMC0716315

URL: https://www.fairviewmicrowave.com/mcx-male-smb-plug-cable-rg316-coax-fmc0716315-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
mue ICX Plug (Male) to SMB Plug (Male) Cable RG-316	DWG NO FMC0716315-XX				CAGE CODE 3FKR5		
Coax Up To 3 GHz, 1.35 VSWR	CAD FILE 102114	SHEET	SCALE	E N/A	SIZE A	5568	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689