

# FMC1828315LF DATA SHEET

# SMC Plug to RA SMC Plug Cable RG-316 Coax with LF Solder

The SMC plug to RA SMC plug cable using RG-316 coax, part number FMC1828315LF, from Fairview Microwave is in-stock and ships same day. This Fairview SMC to SMC cable assembly has a plug to plug gender configuration with 50 ohm flexible RG-316 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1828315LF SMC plug to SMC plug cable assembly operates to 3 GHz. The right angle SMC interface on the RG-316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### **Electrical Specifications**

Description	Min	Ty	ур Мах	Units		
Frequency Range	DC		3	GHz		
Velocity of Propagation		7	0	%		
Capacitance		32 [104.99]		pF/ft [pF/m]		

#### **Mechanical Specifications**

#### **Cable Assembly**

Length\*

Cable

Cable Type Impedance

Inner Conductor Type

Inner Conductor Material and Plating

Dielectric Type Number of Shields

Shield Laver 1

Shield Laver 2

Jacket Material

Jacket Diameter

0 in [0 mm]

RG-316 50 Ohms

Solid

Copper, Silver

**PTFE** 

----

Silver Plated Copper Tape Silver Plated Copper Braid

FEP, Black

0.098 in [2.49 mm]

### **Configuration:**

- SMC Plug
- SMC Plug Right Angle
- RG-316

#### **Features:**

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket

#### **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





#### **Connectors**

Connector 1	Connector 2
SMC Plug	SMC Plug
50 Ohms	50 Ohms
Beryllium Copper, Gol	d Beryllium Copper, Gold
50μ in. minimum	50µ in. minimum
Teflon	Teflon
Brass, Gold	Brass, Gold
3μ in. minimum	3μ in. minimum
4-Jan inch	4-Jan inch
	SMC Plug 50 Ohms Beryllium Copper, Gol 50µ in. minimum Teflon Brass, Gold 3µ in. minimum

#### **Environmental Specifications**

**Temperature** 

Operating Range

-65 to +165 deg C

**Compliance Certifications** (see product page for current document)

## **Plotted and Other Data**

Notes:

#### **How to Order**

Part Number Configuration:

FMC1828315LF - xx uu cm = Centimeters <br/>
<br/>
dlank> = Inches Length

Example: FMC1828315LF-12 = 12 inches long cable

FMC1828315LF-100cm = 100 cm long cable

SMC Plug to RA SMC Plug Cable RG-316 Coax with LF Solder from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: SMC Plug to RA SMC Plug Cable RG-316 Coax with LF Solder FMC1828315LF

URL: https://www.fairviewmicrowave.com/smc-plug-ra-smc-plug-cable-rg316-coax-fmc1828315lf-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

REV 1 Page 2 of 3 Copyright © 2020







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].						
SMC Plug to RA SMC Plug Cable RG-316 Coax with L	DWG NO FMC1828315-XX			CAGE CODE 3FKR5			
Solder	CAD FILE 103114	SHEET	SCALE	N/A	SIZE A	5568	