

RP TNC Female Bulkhead Connector Clamp/Solder Attachment for FM-SR086ALTN, FM-SR086TB, RG405, .480 inch D Hole

RP TNC female bulkhead connector with clamp/solder attachment for FM-SR086ALTN, FM-SR086TB and RG405 (.480 inch D hole), part number FMCN1876, from Fairview Microwave is in-stock and ships same day. Our reverse polarity female configuration uses a female connector body with a male inner contact pin. Fairview's FMCN1876 bulkhead TNC connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's RP TNC female bulkhead connector FMCN1876 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Mechanical Specifications

Size	
Length	1.15 in [29.21 mm]
Width/Dia.	0.512 in [13.00 mm]
Height	0.5 in [12.7 mm]
Weight	0.061 lbs [27.67 g]

Material Specifications

Description	Material	Plating
Body	Brass	Nickel

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Configuration:

- TNC Female Reverse Polarity Connector
- 50 Ohms
- Straight Body Geometry
- FM-SR086ALTN, FM-SR086TB, RG405 Interface Type
- Clamp/Solder Attachment
- Bulkhead

Features:

- Reverse Polarity

Applications:

- General Purpose Test
- Rack and Panel Mount Applications
- Custom Cable Assemblies

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


RP TNC Female Bulkhead Connector Clamp/Solder Attachment for FM-SR086ALTN, FM-SR086TB, RG405, .480 inch D Hole from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RP TNC Female Bulkhead Connector Clamp/Solder Attachment for FM-SR086ALTN, FM-SR086TB, RG405, .480 inch D Hole FMCN1876](#)

URL: <https://www.fairviewmicrowave.com/tnc-female-reverse-polarity-fm-sr086altn-fm-sr086tb-rg405-connector-fmcn1876-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





RP TNC Female Bulkhead Connector Clamp/Solder Attachment for FM-SR086ALTN, FM-SR086TB, RG405, .480 inch D Hole