



# MMCX Jack Connector Crimp/Solder Attachment For .100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100-FR Cable

MMCX jack connector with crimp/solder attachment for .100 inch, RG316, RG174, RG188, LMR-100, LMR-100A and LMR-100-FR, part number SC9561, from Fairview Microwave is in-stock and ships same day. This MMCX jack connector operates up to a maximum frequency of 6 GHz and offers excellent VSWR of 1.22:1.

Fairview's MMCX jack connector SC9561 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

### **Electrical Specifications**

Min	Тур	Max	Units
DC		6	GHz
		1.22:1	
		250	Vrms
		.,,,	DC 6 1.22:1

### **Mechanical Specifications**

**Size** Length Width/Dia.

Weight

0.539 in [13.69 mm] 0.165 in [4.19 mm]

0.006 lbs [2.72 g]

### **Material Specifications**

Description	Material	Plating
Contact	Beryllium Copper	Gold 30 µin minimum
Insulation	PTFE	
Body	Brass	Gold 3 µin minimum

# **Environmental Specifications Temperature**

Operating Range -55 to +155 deg C

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:



## **Configuration:**

- MMCX Jack Connector
- BS EN 122340
- 50 Ohms
- Straight Body Geometry
- .100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100-FR Interface Type
- Crimp/Solder Attachment

#### Features:

- Operating Frequency of 6 GHz Max.
- Excellent VSWR of 1.22:1
- Gold Plated Beryllium Copper Contact
- · 30 µin minimum contact plating

## **Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





MMCX Jack Connector Crimp/Solder Attachment For .100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100-FR Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: MMCX Jack Connector Crimp/Solder Attachment For .100 inch, RG316, RG174, RG188, LMR-100, LMR-100A, LMR-100-FR Cable SC9561

URL: https://www.fairviewmicrowave.com/mmcx-jack-standard-rg174-rg316-rg188-connector-sc9561-p.aspx







