



RA SMA Female to RP SMA Male Adapter

RA SMA female to RP SMA male adapter part number SM4997 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to reverse polarity SMA adapter has a female to male gender configuration. SM4997 SMA female to reverse polarity SMA male adapter operates to 6 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. This low profile right angle SMA adapter allows for easier connections in tight spaces. The Fairview Microwave RF adapter provides excellent VSWR of 1.25:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connnector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units		
Frequency Range	DC		6	GHz		
VSWR			1.25:1			

Electrical Specification Notes: Values at 25° C, sea level.

Mechanical Specifications

Size	
Length	0.62 in [15.75 mm]
Width	0.583 in [14.81 mm]
Weight	0.01014 lbs [4.6 g]

Description	Connector 1	Connector 2
Туре	SMA Female	SMA Male
Polarity	Standard	Reverse Polarity
Interface Specification	MIL-STD-348	MIL-STD-348
Mating Cycles	500	500



Configuration:

- SMA Female Connector 1
- SMA Male Reverse Polarity Connector 2
- 50 Ohms
- Right Angle Body Geometry

Features:

- VSWR of 1.25:1 max up to 6 GHz
- SMA interface meets MIL-STD-348
- · Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

Applications:

mm]

General Purpose Test

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications


Connector 1	Connector 2			
SMA Female	SMA Male			
Beryllium Copper	Beryllium Copper			
Gold	Gold			
MIL-G-45204	MIL-G-45204			
PTFE	PTFE			
Brass				
Nickel				
QQ-N-290				
	Brass			
	Nickel			
	QQ-N-290			
	SMA Female Beryllium Copper Gold MIL-G-45204 PTFE Brass Nickel			

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







RA SMA Female to RP SMA Male Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: RA SMA Female to RP SMA Male Adapter SM4997


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order

URL: https://www.fairviewmicrowave.com/ra-sma-female-rp-sma-male-adapter-sm4997-p.aspx

to impleme	ent improven	nents. Fairview	Microwa	ave reserv	es the righ	nt to mak	ke such	changes	as requ	ired. Unles	s otl	herwise
		s are nominal.										
suitability	of the part d	escribed hereir	for any	particular	purpose,	and Fair	rview M	icrowave	does n	ot assume	any	liability
arising out	of the use o	f any part or do	ocument	ation.								







FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
RA SMA Female to RP SMA Male Adapter	DWG NO SM4997				CAGE CODE 3FKR5		
	CAD FILE 112414	SHEET	SCAL	E N/A	SIZE A	150	