

SMW51AC DATA SHEET

WR-51 to SMA Female Waveguide to Coax Adapter UBR180 Flange With 15 GHz to 22 GHz Frequency Range For Ku-K Band

The SMW51AC is a waveguide to coaxial adapter with a frequency range of 15 to 22 GHz, operating in the Ku-K band. This adapter offers a precision tolerance UBR180 flange and a WR-51 waveguide interface size. SMW51AC is constructed of copper to ensure durability and repeatable RF performance. The SMA female connector mates with commercially available 2.92mm and 3.5mm connectors. The package is REACH and RoHS compliant.

Configuration

Waveguide Size Flange RF Connector Body Geometry WR-51 UBR180 SMA Female Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	15		22	GHz
VSWR			1.25:1	
Insertion Loss		0.4		dB

Mechanical Specifications

Size

 Length
 1.06 in [26.92 mm]

 Width
 1.19 in [30.23 mm]

 Height
 1.19 in [30.23 mm]

 Weight
 0.11288 lbs [51.2 g]

RF Connector

 $\begin{array}{ccc} \text{Connector Type} & & \text{SMA Female} \\ \text{Specification} & & 30 \mu \text{ in. min.} \end{array}$

Contact Material and Plating

Body Material and Plating

Passivated Stainless Steel
Torque

Beryllium Copper, Gold
Passivated Stainless Steel
8 in-lbs [0.9 Nm]

Waveguide Interface

Waveguide Type WR-51
Flange Type UBR180
Body Material and Plating Copper

Environmental Specifications

Temperature

Operating Range -55 to +120 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at +25 °C, sea level unless stated otherwise



Features:

- Ku-K Band, 15 to 22 GHz Frequency Range
- WR-51 Waveguide Interface with UBR180 Flange
- SMA Female Coaxial Interface
- Comprehensive waveguide offerings also include E-Bends, H-Bends, Sections, Filters, Terminations, Couplers, and more.


Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com



Typical Performance Data



WR-51 to SMA Female Waveguide to Coax Adapter UBR180 Flange With 15 GHz to 22 GHz Frequency Range For Ku-K Band from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-51 to SMA Female Waveguide to Coax Adapter UBR180 Flange With 15 GHz to 22 GHz Frequency Range For Ku-K Band SMW51AC

URL: https://www.fairviewmicrowave.com/wr-51-sma-female-connector-waveguide-coax-adapter-15-22-ghz-smw51ac-p. aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







STANDARD TOLERANCES

X ±0.2

XX ±0.1

XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
WR-51 to SMA Female Waveguide to Coax Adapter UBR180 Flange With 15 GHz to 22 GHz Frequency Range For Ku-K Band	DWG NO SMW51AC			CAGE CODE 3FKR5			
	CAD FILE 071916	SHEET	SCALE	N/A	SIZE A	3045	