



RA SMA Male to SMA Female Adapter

RA SMA male to SMA female adapter part number SM5265 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to SMA adapter has a male to female gender configuration. SM5265 SMA male to SMA female adapter operates to 12.4 GHz. The Fairview Microwave RF adapter provides good VSWR of 1.3:1 maximum. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. This right angle SMA adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		12.4	GHz
VSWR			1.3:1	
Insertion Loss			0.15	dB

Electrical Specification Notes: Values at 25°C, sea level.

Mechanical Specifications

chamical Specificati	Ulis
Size	
Length	
Height	
Weight	

0.625 in [15.88 mm] 0.585 in [14.86 mm] 0.0145 lbs [6.58 q]

Description	Connector 1	Connector 2	
Туре	SMA Male	SMA Female	
Polarity	Standard	Standard	
Interface Specification	MIL-STD-348	MIL-STD-348	
Mating Cycles	500	500	
Mating Torque	8 to 10 in-lbs		
	[0.90 to 1.13 Nm]		



Configuration:

- SMA Male Connector 1
- SMA Female Connector 2
- 50 Ohm
- Right Angle Body Geometry

Features:

- VSWR of 1.3:1 max up to 12.4 GHz
- SMA interface meets MIL-STD-348
- Contact plating according to MIL-G-45204
- Gold Plated Beryllium Copper Contact

Applications:

General Purpose Test

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





Material Specifications

Description	Connector 1	Connector 2			
Туре	SMA Male	SMA Female			
Contact Material	Beryllium Copper	Beryllium Copper			
Contact Plating	Gold	Gold			
Contact Plating Spec.	MIL-G-45204	MIL-G-45204			
Insulation Material	PTFE	PTFE			
Outer Contact Material		Passivated Stainless Steel			
Body Material	Passivated Stainless Steel				

Environmental Specifications

Temperature

Operating Range


-55 to +100 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data







RA SMA Male to SMA Female Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order


For additional information on this product, please click the following link: RA SMA Male to SMA Female Adapter SM5265

URL: https://www.fairviewmicrowave.com/ra-sma-male-sma-female-adapter-sm5265-p.aspx

to implem	ent impr	ovements	 Fairview 	v Microv	ave reserv	es the righ	it to mak	ke such	changes	as requ	uired. Unle	ss oth	nerwise
					w Microwa								
suitability	of the pa	art descri	bed hereir	n for an	y particular	purpose,	and Fair	view M	icrowave	does r	not assume	any	liability
arising ou	t of the u	se of any	part or do	ocumen	tation.								







STANDARD TOLERANCES

.X ±0.2 .XX ±0.1 .XXX ±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
RA SMA Male to SMA Female Adapter	DWG NO	SM5265			CAGE CODE 3FKR5		
	CAD FILE 111416	SHEET	SCAL	E N/A	SIZE A	41742	