



RF Load 1 Watts To 6 GHz Gold Plated Brass MMCX Plug

RF termination (also called RF load or dummy load) ST6022 from Fairview Microwave operates from DC to 6 GHz and handles up to 1 Watt (CW). This MMCX termination (or load) has a plug connection type. ST6022 MMCX load termination offers 1.35:1 max VSWR.

RF terminations / loads are critical passive components in many RF, microwave and millimeter wave systems where signal reflection from unused ports can reduce the signal integrity and can potentially damage the device. By terminating an unused port with a matched load (dummy load), the incident energy will be absorbed with minimal reflection. These radio frequency termination components are commonly used to terminate devices such as couplers, circulators, and switches. Loads / terminations are also widely used in measurement systems to ensure accurate results. Fairview offers a large selection of in-stock RF, microwave and millimeter wave terminations up to 65 GHz with great performance over the entire operating range and with power handling capabilities up to 800 Watts (CW).

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.35:1	
Input Power (CW)			1	Watts

Mechanical Specifications

Size

 Length
 0.47 in [11.94 mm]

 Width
 0.2 in [5.08 mm]

 Weight
 0.0035 lbs [1.59 g]

Configuration

Connector MMCX Plug

Material Specifications

Description	Material	Plating		
Connector 1 Contact	Brass	Gold		
Insulation	PTFE			
Body	Brass	Gold		
Housing	Brass	Gold		

Environmental Specifications Temperature

Operating Range

-45 to +120 deg C



Features:

- DC to 6 GHz Frequency Range
- VSWR 1.35:1 Max
- Max Power 1 Watt (CW)
- MMCX Plug Coaxial Interface

Applications:

- Wireless
- SatCom
- Radar Systems
- Test and Measurement
- Commercial and Military Communication

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Typical Performance Data



RF Load 1 Watts To 6 GHz Gold Plated Brass MMCX Plug from Fairview Microwave is in-stock and available to ship sameday. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RF Load 1 Watts To 6 GHz Gold Plated Brass MMCX Plug ST6022

URL: https://www.fairviewmicrowave.com/rf-load-1-watts-6-ghz-mmcx-plug-st6022-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.







 $\frac{\mathtt{STANDARD\ TOLERANCES}}{\mathtt{DECIMAL}}$

 $\begin{array}{cc} .XX & \pm 0.20 \\ .XXX & \pm 0.10 \end{array}$

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
RF Load 1 Watts To 6 GHz Gold Plated Brass MMCX	DWG NO	ST6022		CAGE CODE 3FKR5		
Plug	CAD FILE 041316	SHEET	SCALI	≣ N/A	SIZE A	3045