


REVISION					
ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/10/2023	SREITER	SPONG



UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

$.X = \pm .2$	[5]	FRACTIONS
$.XX = \pm .02$	[.5]	$\pm 1/32$
$.XXX = \pm .005$	[.13]	ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:

$$\begin{aligned} &\leq 12 \text{ [305]} = +1 \text{ [25]} / -0 \\ &> 12 \text{ [305]} \leq 60 \text{ [1524]} = +2 \text{ [51]} / -0 \\ &> 60 \text{ [1524]} \leq 120 \text{ [3048]} = +4 \text{ [102]} / -0 \\ &> 120 \text{ [3048]} \leq 300 \text{ [7620]} = +6 \text{ [152]} / -0 \\ &> 300 \text{ [7620]} = +5\% / -0 \end{aligned}$$

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.



Fairview Microwave®
an INFINIT® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678

DESCRIPTION

20dB RF FIXED ATTENUATOR 4.3-10 FEMALE TO FEMALE
600MHz TO 6GHz, 50W AND LOW PIM

SIZE	A
------	---


E	CAGE CODE 3FKR5
---	--------------------

E	DRAWN BY SREITER
---	----------------------------

ITEM NO.	DESCRIPTION	QTY	UNIT	AMOUNT
----------	-------------	-----	------	--------

FMAT7481-20

REV
A



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE
NO

SHEET
1 OF 1

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.