

6

5

4

3

2

1

REVISION

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	03/10/2023	SREITER	SPONG

1.54
[39.0]
TYP..33
[8.5]
TYP.7.48
[190.0]3.74
[95.0].79
[20.0]
TYP.5.51
[140.0]
TYP.10.63
[270.0]8X ϕ .22 [5.5]
MOUNTING HOLEN-TYPE FEMALE
CONNECTOR.85
[21.5]1.67
[42.5]3.74
[95.0]

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:

.X = $\pm$.2	[5]	FRACTIONS
.XX = $\pm$.02	[.5]	$\pm$ 1/32
.XXX = $\pm$.005	[.13]	ANGLES $\pm$ 1°

CABLE LENGTH TOLERANCES:


≤ 12 [305]	= +1 [25] / -0
>12 [305] $\leq$ 60 [1524]	= +2 [51] / -0
>60 [1524] $\leq$ 120 [3048]	= +4 [102] / -0
>120 [3048] $\leq$ 300 [7620]	= +6 [152] / -0
>300 [7620]	= +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.



Fairview Microwave®
an INFINITE® brand

Website: www.FairviewMicrowave.com
Phone: 1.800.715.4396 | 1.972.649.6678



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE

NONE

SHEET

1 OF 1

DESCRIPTION

RF TERMINATION N-TYPE FEMALE 400MHZ TO 6GHz 300W,
LOW PIM

SIZE

A

CAGE CODE

3FKR5

DRAWN BY

SREITER

ITEM NO.

FMTR1156

REV

A

6

5

4

3

2

1