

## Tab pin & dielectric for 0.46mm (.018inch) field replaceable connector



### FM1016-16

#### Applications

- General Purpose Test
- Rack and Panel Mount Applications
- Used in Field Replaceable Connectors
- Allows for Replacement of Damaged Connectors

#### Description

Fairview Microwave's FM1016-16 Tab pin & dielectric for 0.46mm (.018inch) field replaceable connector is part of our complete line of Connector Launch Accessories available for same-day shipping. This range of accessories includes Glass bead Transitions, Launch Pin & Dielectric Transitions and Pin/Tab Transitions to Microstrip and Stripline Circuits in conjunction with our line of field replaceable flange connectors. These accessories are designed to be compatible with our line of Field Replaceable Connectors to ensure optimal electrical performance for PCB test applications. They are available in commonly used pin diameters of .009", .012", .015", .018", .020" and .036" and in a variety of lengths and sizes depending on the application.

Our FM1016-16 Tab pin & dielectric for 0.46mm (.018inch) field replaceable connector datasheet specifications are shown below in this PDF. Fairview Microwave's broad catalog of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Fairview Microwave has the right connector for the job. Fairview Microwave can also expertly build your custom cable assemblies for you and ship same day.

#### Mechanical Specifications

##### Dimensions

Pin Length	0.275 in [6.99 mm]
Pin Diameter	0.059 in [1.5 mm]
Tab Length	0.05 in [1.27 mm]
Tab Diameter	0.059 in [1.5 mm]
Dielectric Length	0.187 in [4.75 mm]
Dielectric Diameter	0.059 in [1.5 mm]
Dielectric Material	PTFE
Conn End Pin Length	0.018 in [0.46 mm]
Weight	0.00007 lbs [0.03 g]

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Tab pin & dielectric for 0.46mm (.018inch)  
field replaceable connector



## FM1016-16

Tab pin & dielectric for 0.46mm (.018inch) field replaceable connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Tab pin & dielectric for 0.46mm \(.018inch\) field replaceable connector FM1016-16](#)

URL: <https://www.fairviewmicrowave.com/product/hermetic-seal-solder-contact-0.059-pin-diameter-0.018-body-0.275-pin-fm1016-16.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

# FM1016-16 CAD Drawing

Tab pin & dielectric for 0.46mm (.018inch) field replaceable connector

