

Bulkhead TNC Female (Jack) to TNC Female (Jack) Adapter, Commercial Grade

FMAD10067



Configuration

- TNC Female Connector 1
- TNC Female Connector 2
- 50 Ohms Impedance
- Straight Body Geometry
- Bulkhead Mount Method

Features

- Gold Plated Phosphor Bronze Contact

Applications

- General Purpose Test
- Rack Mounted Equipment

Description

Bulkhead TNC female to TNC female adapter part number FMAD10067 from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC adapter has a female to female gender configuration. FMAD10067 TNC female to TNC female adapter. Our RF TNC bulkhead to TNC adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Impedance		50		Ohms

Mechanical Specifications

Size

Length	1.29 in [32.77 mm]
Width	0.74 in [18.80 mm]
Height	0.74 in [18.80 mm]
Weight	0.04 lbs [18.14 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	TNC Female		TNC Female	

Bulkhead TNC Female (Jack) to TNC Female (Jack) Adapter, Commercial Grade



FMAD10067

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Contact	Phosphor Bronze	Gold	Phosphor Bronze	Gold
Insulation	POM		POM	
Outer Conductor	Brass	Nickel	Brass	Nickel
Body	Brass	Nickel	Zinc Alloy	Nickel
Washer	Steel	Nickel		
Coupling Nut	Brass	Nickel		

Compliance Certifications (see [product page](#) for current document)

Bulkhead TNC Female (Jack) to TNC Female (Jack) Adapter, Commercial Grade from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Bulkhead TNC Female \(Jack\) to TNC Female \(Jack\) Adapter, Commercial Grade FMAD10067](#)

URL: <https://www.fairviewmicrowave.com/product/rf-adapters/bulkhead-tnc-female-to-tnc-female-adapter-fmad10067.html>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

Bulkhead TNC Female (Jack) to TNC Female (Jack) Adapter, Commercial Grade

