

**SMP Female to Smooth Bore SMP Male Bulkhead
 Cable FM-F086 Coax in 24 Inch**

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		16	GHz
VSWR			1.35:1	

Mechanical Specifications

Cable Assembly

Length	24 in [609.6 mm]
Weight	0.025 lbs [11.34 g]

Cable

Cable Type	FM-F086
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Tape
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Blue
Jacket Diameter	0.209 in [5.31 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMP Female	SMP Male Bulkhead
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Spec.	30µ in. minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material & Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Spec.	30µ in. minimum	MIL-G-45204

Environmental Specifications

Temperature

Operating Range	-65 to +165 deg C
-----------------	-------------------

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:




Configuration:

- SMP Female
- SMP Male Bulkhead
- FM-F086

Fairview Microwave
 1130 Junction Dr. #100
 Allen, TX 75013
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Typical Performance Data



How to Order

Part Number Configuration:

FMC2233085 - xx uu

cm = Centimeters
<blank> = Inches
Length


Example: FMC2233085-12 = 12 inches long cable
FMC2233085-100cm = 100 cm long cable

SMP Female to Smooth Bore SMP Male Bulkhead Cable FM-F086 Coax in 24 Inch from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and fiber optic products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMP Female to Smooth Bore SMP Male Bulkhead Cable FM-F086 Coax in 24 Inch FMC2233085-24](#)

URL: <http://www.fairviewmicrowave.com/standard-smp-female-smp-male-cable-fmf086-coax-fmc2233085-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE SMP Female to Smooth Bore SMP Male Bulkhead Cable FM-F086 Coax in 24 Inch		DWG NO FMC2233085		CAGE CODE 3FKR5	
CAD FILE	103114	SHEET	SCALE	N/A	SIZE A 5568