

Low PIM SMA Male to 7/16 DIN Male LSZH Jacketed Cable 0.141 Formable Low PIM Coax in 100 CM

The SMA male to 7/16 DIN male 100 cm cable using 0.141 Formable low PIM coax, part number FMC0215951-100CM, from Fairview Microwave is in-stock and ships same day. This Fairview SMA to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm formable 0.141 formable low PIM coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. Our low PIM design offers excellent passive intermodulation performance with PIM levels better than -150 dBc. The FMC0215951-100CM SMA male to 7/16 DIN male cable assembly operates to 3 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		3	GHz
VSWR			1.15:1	
RF Shielding	-100			dB
Passive Intermodulation			-150	dBc
Input Power (Average)			440	Watts

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	2.5	3	GHz
Insertion Loss (Typ.)	0.27	0.41	0.6	0.68	0.75	dB
Power Handling (Max.)	440	300	220	190	170	W

Mechanical Specifications

Cable Assembly

Length*	39.37 in [100 cm]
Weight	0.0102 lbs [4.63 g]

Cable

Cable Type	0.141 Formable Low PIM
Impedance	50 Ohms
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Outer Conductor Material and Plating	Copper, Tin
Jacket Material	PVC LSZH
Jacket Diameter	0.163 in [4.14 mm]

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------



Configuration:

- SMA Male
- 7/16 DIN Male
- 0.141 Formable Low PIM

Features:

- Max Frequency 3 GHz
- Low PIM: -150 dBc Max
- Shielding Effectivity > -100 dB
- PVC LSZH Jacket

Applications:

- General Purpose
- Laboratory Use
- Low PIM Applications

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	7/16 DIN Male
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Brass, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material & Plating	Brass, Silver	Brass, Silver
Coupling Nut Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal
Hex Size	5/16 inch	1 1/4 inch

Environmental Specifications
Temperature

Operating Range

-55 to +125 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

FMC0215951 - xx uu

 cm = Centimeters
 <blank> = Inches

Length


 Example: FMC0215951-12 = 12 inches long cable
 FMC0215951-100cm = 100 cm long cable

Low PIM SMA Male to 7/16 DIN Male LSZH Jacketed Cable 0.141 Formable Low PIM Coax in 100 CM from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [Low PIM SMA Male to 7/16 DIN Male LSZH Jacketed Cable 0.141 Formable Low PIM Coax in 100 CM FMC0215951-100CM](#)

URL: <https://www.fairviewmicrowave.com/sma-male-7-16-male-cable-0.141-formable-low-pim-coax-fmc0215951-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE Low PIM SMA Male to 7/16 DIN Male LSZH Jacketed Cable 0.141 Formable Low PIM Coax in 100 CM		DWG NO FMC0215951		CAGE CODE 3FKR5	
CAD FILE	120314	SHEET		SCALE	N/A
			SIZE	A	2233