

SMP Female to SMA Male Cable FM-SR405FL Coax

The SMP female to SMA male cable using FM-SR405FL coax, part number SCA78086, from Fairview Microwave is in-stock and ships same day. This Fairview SMP to SMA cable assembly has a female to male gender configuration with 50 ohm formable FM-SR405FL coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The SCA78086 SMP female to SMA male cable assembly operates to 12 GHz. The SMP female to SMA male cable using RG405 type .086 coax, part number SCA78086, from Fairview Microwave is in-stock and ships same day. This Fairview SMP to SMA cable assembly has a female to male gender configuration with 50 ohm formable FM-SR405FL coax. Fairview Microwave's formable RF cable assemblies provide an alternative to costly pre-formed semi-rigid assemblies since they are hand formable. The SCA78086 SMP female to SMA male cable assembly operates to 12 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	DC		12	GHz
VSWR			1.35:1	

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	5	10		GHz
Insertion Loss (Typ.)	0.15	0.22	0.5	0.8		dB/ft
	0.49	0.72	1.64	2.62		dB/m

Electrical Specification Notes:

Insertion loss does not include the loss of the connectors.

Insertion loss is estimated as $0.05 \times \sqrt{f(\text{GHz})}$ dB per connector.

Mechanical Specifications

Cable Assembly

Length* 0 in [0 mm]

Cable

Cable Type FM-SR405FL
Impedance 50 Ohms



Configuration:

- SMP Female
- SMA Male
- FM-SR405FL


Features:

- Max Frequency 12 GHz
- Max Frequency 12 GHz

Applications:

- General Purpose
- Laboratory Use
- General Purpose
- Laboratory Use

Cable Diagram:



Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Tinned Copper Braid
Outer Conductor Diameter	0.086 in [2.18 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMP Female	SMA Male
Configuration	Straight	Straight
Impedance	50 Ohms	50 Ohms
Contact Material & Plating	Beryllium Copper, Gold	Brass, Gold
Dielectric Type		PTFE
Body Material & Plating	Beryllium Copper, Gold	Brass, Gold
Coupling Nut Material & Plating		Brass, Nickel
Hex Size		5/16 inch
Torque		5 in-lbs 0.57 Nm

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:

SCA78086 - xx uu

cm = Centimeters
 <blank> = Inches
 Length


Example: SCA78086-12 = 12 inches long cable
 SCA78086-100cm = 100 cm long cable

SMP Female to SMA Male Cable FM-SR405FL Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: [SMP Female to SMA Male Cable FM-SR405FL Coax SCA78086](#)

URL: <https://www.fairviewmicrowave.com/smp-female-sma-male-cable-sf-085-coax-sca78086-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.1
.XXX	±0.05

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

FAIRVIEW MICROWAVE INC.

ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

TITLE SMP Female to SMA Male Cable FM-SR405FL Coax	DWG NO SCA78086		CAGE CODE 3FKR5		
	CAD FILE 102016	SHEET	SCALE N/A	SIZE A	41742