

Rubber Duck Portable Antenna Operates From 2.4 GHz to 2.5 GHz With a Nominal 5.5 dBi Gain SMA Male Connector

Rubber duck portable antenna FM51078 from Fairview Microwave (also known as a rubber ducky antenna) is part of our extensive in-stock omni-directional radio antenna selection. This single band rubber duck portable antenna has a frequency range of 2.4 GHz to 2.5 GHz and a 5.5 nominal dBi gain. Our portable rubber duck antenna uses SMA male connector and is rated for 0 Watts input. FM51078 rubber duck portable radio antenna is one of over 40,000 RF, microwave and millimeter wave components supplied from Fairview Microwave. Our portable rubber duck aerial can be bought and shipped worldwide the same-day as with our other available RF parts.

Configuration

Design	Portable
Polarization	Vertical
Connector Type	SMA Male Reverse Polarity

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	2,400		2,500	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain	5.5			dBi

Mechanical Specifications

Radome Material	PU
Size	
Length	7.8 in [198.12 mm]
Width	0.516 in [13.11 mm]
Height	0 in [0 mm]
Weight	0.028 lbs [12.7 g]

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:

- Vertical Polarized
- Tilt and Swivel Rubberduck / External Dipole
- 2.4 to 2.5 GHz
- 5.5 dBi gain
- RP-SMA Male Connector

Applications:

- 2.4 GHz Wi-Fi
- IoT
- Zigbee, Bluetooth

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

Rubber Duck Portable Antenna Operates From 2.4 GHz to 2.5 GHz With a Nominal 5.5 dBi Gain SMA Male Input Connector from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Rubber Duck Portable Antenna Operates From 2.4 GHz to 2.5 GHz With a Nominal 5.5 dBi Gain SMA Male Input Connector FM51078](#)

URL: <https://www.fairviewmicrowave.com/dbi-rubber-duck-portable-antenna-2400-2500-mhz-sma-connector-fm51078-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



