

FM9864B-20 DATA SHEET

WR-430 Standard Gain Horn Antenna Operating From 1.7 GHz to 2.6 GHz, 20 dBi Nominal Gain, CPR-430F Flange, ProLine

The Pro-series WR-430 FM9864B-20 standard gain horn antenna (also known as waveguide horn) from Fairview Microwave has a nominal gain of 20 dBi. The Fairview Microwave 20 dBi WR-430 horn antenna operates from 1.7 GHz to 2.6 GHz. This WR-430 standard gain horn has a CPR-430F type flange. The WR-430 FM9864B-20 waveguide horn is part of over 40,000 RF, microwave and millimeter wave components available from Fairview Microwave. Waveguide standard gain horn antennas are used in a wide variety of applications due to their high power handling capability, low loss, high directivity, and near constant electrical performance. The Pro-series gain horns are US made and TAA compliant. Fairview Microwave's WR-430 standard gain horns are available in 10, 15 and 20 dBi models with pyramidal shape and rectangular input. Pro-series WR-430 standard gain horn antenna can ship the same day to anywhere in the world.



Design WR-430 Standard Gain Horn

Pattern Directional Polarization Linear

Electrical Specifications

| Description | Min | Тур | Max | Units |
|-----------------|-----|-------|-----|-------|
| Frequency Range | 1.7 | | 2.6 | GHz |
| Nominal Gain | | 20 | | dB |
| VSWR | | 1.5:1 | | |
| | | | | |

Mechanical Specifications

Size

 Length
 40.5 in [102.87 cm]

 Width/Diameter
 22 in [558.8 mm]

 Height
 16 in [406.4 mm]


Waveguide Interface

Waveguide Size WR-430
Flange Type CPR-430F
Body Material and Plating Aluminum

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:



Features:

- WR-430 Rectangular Waveguide Interface
- 1.7 GHz to 2.6 GHz
- 20 dBi Nominal Gain
- CPR-430F Cover Flange

Applications:

- Antenna Measurements
- Wireless Communication
- Laboratory Use
- Microwave Radio System

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





WR-430 Standard Gain Horn Antenna Operating From 1.7 GHz to 2.6 GHz, 20 dBi Nominal Gain, CPR-430F Flange, ProLine from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-430 Standard Gain Horn Antenna Operating From 1.7 GHz to 2.6 GHz, 20 dBi Nominal Gain, CPR-430F Flange, ProLine FM9864B-20

URL: https://www.fairviewmicrowave.com/wr-430-waveguide-standard-gain-horn-20-db-fm9864b-20-p.aspx

