

2400-2500 MHz, 1.74 dBi, Stamped Metal AP/Router Embedded Antenna-50 Pack

Fairview Microwave's FMSMA1013-50PK is a linear polarized antenna that ships same day from our ISO 9001:2015 certified facility. The FMSMA1013-50PK is a single-band antenna with a maximum frequency of 2500 MHz and a minimum frequency of 2400 MHz. This 50-pack stamped metal antenna has a nominal gain of 1.74 dBi.

Fairview Microwave's stamped metal antenna with a 2400 to 2500 MHz frequency range has a maximum input VSWR of 2. The FMSMA1013-50PK antenna has an overall length of 0.99 inches and a width of 0.06 inches. This 50-pack omni directional antenna has an impedance of 50 Ohms.

Additional dimensions and specifications for these stamped metal antennas are on our downloadable PDF datasheet above. Our technical experts are on hand to assist you with any inquiries. Use our online ordering system to purchase your FMSMA1013-50PK antenna 24 hours a day with same-day shipping and no MOQs (minimum order quantities).

Configuration

Design	Stamped Metal
Gain	1.74
Polarization	Linear

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	2,400		2,500	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Gain		1.74		dBi
Input Power			1	Watt

Mechanical Specifications

Size	
Length	0.99 in [25.15 mm]
Width	0.06 in [1.52 mm]
Height	0.18 in [4.57 mm]


Environmental Specifications

Temperature	
Operating Range	-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:

- High Efficiency
- Isotropic radiation patterns
- Linear polarization
- Ultra-Compact design
- Low loss material - Nickel-Plated brass
- Extended operating temperatures
- On board mount
- Frequency stabilization
- 50-pack for easy buy

Applications:

- IoT, M2M, Telemetry
- Wireless Remote Control
- Personal Area Networks(PAN)
- Industrial/Commercial Equipment
- 2.4/5 GHz - Wi-Fi/BT/BLE/ZigBee/ISM applications
- IEEE802.11a/b/g/n/ac embedded applications
- Remote Technology / Monitoring
- Consumer Tracking
- Smart Home / Wearables / Devices
- Agriculture, healthcare, digital signage

Fairview Microwave
 301 Leora Ln., Suite 100
 Lewisville, TX 75056
 Tel: 1-800-715-4396 / (972) 649-6678
 Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

2400-2500 MHz, 1.74 dBi, Stamped Metal AP/Router Embedded Antenna-50 Pack from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [2400-2500 MHz, 1.74 dBi, Stamped Metal AP/Router Embedded Antenna-50 Pack FMSMA1013-50PK](#)

URL: <https://www.fairviewmicrowave.com/1.74-stamped-metal-antenna-2400-2500-mhz-4694r-br-connector-fms-ma1013-50pk-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

