


SMA Female (Jack) Connector Terminal 4 Hole Flange (Panel) Dummy Panel Mount, Solder, Passivated Stainless Steel Body, Length 0.375 In



SC4291

Configuration

- SMA Female Connector
- 50 Ohms
- Straight Body Geometry
- Connector Interface Types: Panel Mount Dummy
- 4 Hole Flange

Features

- Operating Frequency of DC Max.

Applications

- General Purpose Test
- Rack and Panel Mount Applications

Description

SMA Female Connector Solder Attachment for Panel Mount Dummy Cable,, part number SC4291, from Fairview Microwave is in-stock and ships same day. This SMA female connector operates up to a maximum frequency of DC. Fairview's SC4291 4 hole flange SMA connector enables designers to make external connections on product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Fairview's SMA female 4 hole flange connector SC4291 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		0	KHz
Impedance		50		Ohms

Mechanical Specifications


Size

Length	0.375 in [9.53 mm]
Width	0.5 in [12.7 mm]
Height	0.5 in [12.7 mm]
Weight	0.0065 lbs [2.95 g]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	
Insulation	PTFE	
Outer Conductor	Stainless Steel	Passivated
Body	Stainless Steel	Passivated
		MIL-PRF-39012

SMA Female (Jack) Connector Terminal 4 Hole Flange
(Panel) Dummy Panel Mount, Solder, Passivated
Stainless Steel Body, Length 0.375 In



SC4291

Environmental Specifications

Temperature

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Female (Jack) Connector Terminal 4 Hole Flange (Panel) Dummy Panel Mount, Solder, Passivated Stainless Steel Body, Length 0.375 In from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [SMA Female \(Jack\) Connector Terminal 4 Hole Flange \(Panel\) Dummy Panel Mount, Solder, Passivated Stainless Steel Body, Length 0.375 In SC4291](#)

URL: <https://www.fairviewmicrowave.com/product/rf-connectors/sma-female-panel-mount-dummy-terminal-connector-sc4291>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

SMA Female (Jack) Connector Terminal 4 Hole Flange (Panel) Dummy Panel Mount, Solder, Passivated Stainless Steel Body, Length 0.375 In

