

FMW19SP4 DATA SHEET

WR-19 Waveguide Short Plate with 4mm Copper and UG-Cover Round Flange

FMW19SP4 is a fixed WR-19 waveguide short (shorting plate) with operating frequency range from 40 GHz to 60 GHz. This waveguide short is fabricated with 4 mm thick copper by high precision manufacturing process. FMW19SP4 has a Round UG-Cover configuration and provides high reflection short circuit for WR-19 waveguide components. Along with Fairview Microwave's waveguide shim products, the waveguide short is ideal for TRL (Thru, Reflect, Line) calibration for RF test instruments. Fairview Microwave offers a wide selection of waveguide components with high performance available in stock and same-day shipping to customers worldwide.

Mechanical Specifications

 Body Material
 Copper

 Body Finish
 Gold Plating

 Length
 0.158 in [4.01 mm]

 Width
 1.126 in [28.6 mm]

 Height
 1.126 in [28.6 mm]

 Weight
 0.022 lbs [9.98 g]

Compliance Certifications (see product page for current document)

WR-19 Waveguide Short Plate with 4mm Copper and UG-Cover Round Flange from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: WR-19 Waveguide Short Plate with 4mm Copper and UG-Cover Round Flange FMW19SP4

URL: https://www.fairviewmicrowave.com/undefined-url-for-pn-fmw19sp4-fmw19sp4-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



Features:

- · WR-19 Waveguide Short Plate
- Round UG-Cover Flange Configuration
- Frequency Range: 40 GHz to 60 GHz
- Min VSWR: 60:1
- 4 mm Thick Copper Construction

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com

sales@fairviewmicrowave.com





