

RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, 1.2 VSWR



SM4537

Configuration

- N Male Connector 1
- N Female Connector 2
- 50 Ohms Impedance
- Right Angle Body Geometry

Features

- VSWR of 1.2:1 max up to 6 GHz

Applications

- General Purpose Test

Description

RA type N male to type N female adapter part number SM4537 from Fairview Microwave is in-stock and ships same day. This Fairview type N to type N adapter has a male to female gender configuration. SM4537 type N male to type N female adapter operates to 6 GHz. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum. This right angle type N adapter allows for easier connections in tight spaces.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
Impedance		50		Ohms
VSWR			1.2:1	


Mechanical Specifications

Size

Length	1.38 in [35.05 mm]
Height	1.30 in [33.02 mm]
Weight	0.13 lbs [58.51 g]

Description	Connector 1	Connector 2
Polarity	Standard	Standard

RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, 1.2 VSWR



SM4537

Material Specifications

Description	Connector 1		Connector 2	
	Material	Plating	Material	Plating
Type	N Male		N Female	
Contact		Gold		Gold
Insulation	PTFE		PTFE	
Outer Conductor			Brass	Nickel
Body	Brass	Nickel		

Compliance Certifications (see [product page](#) for current document)

RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, 1.2 VSWR from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [RA N Male \(Plug\) to N Female \(Jack\) Adapter, Nickel Plated Brass Body, 1.2 VSWR SM4537](#)

URL: <https://www.fairviewmicrowave.com/product/rf-adapters/ra-n-male-to-n-female-adapter-sm4537>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

SM4537 CAD Drawing

RA N Male (Plug) to N Female (Jack) Adapter, Nickel Plated Brass Body, 1.2 VSWR

