

FM-SR141TB-BULK **DATA SHEET**

.141 Semi-rigid Formable Coax Cable Jacket

Formable semi-rigid coax is a hand formable version of standard semi-rigid that does not require complicated and costly preformed cable assemblies. Because the dimensions and electrical characteristics are so closely matched to semi-rigid coax, standard semi-rigid connectors can be used. The tin soaked copper braid outer shield provides excellent RF shielding.

Electrical Specifications

Description	Min	Т	ур	Max	Units	
Frequency Range	DC			20	GHz	
Impedance		50 Oh		Ohms		
Velocity of Propagation		69	9.5	%		
Shielding Effectiveness	110				dB	
Inner Conductor DC Resist.				7.8	Ohms/1000ft	
Outer Conductor DC Res	ist.			5.5	Ohms/1000ft	
Nominal Capacitance		2	29		pF/ft	
		[95	5.14]		[pF/m]	

Performance by Frequency Band								
Description	F1	F2	F3	F4	F5			
Frequency	0.5	1	5	10	20			

Units GHz 8 29 45 70 Attenuation, Typ 12 dB/100ft 26.25 39.37 95.14 147.64 229.66 dB/100m

Mechanical Specifications

Min. Bend Radius (Repeated)

0.625 in [15.88 mm]

Construction Specifications

Description	Material and Plating	Diameter
Inner Conductor	Copper, Silver, 1 Strands	0.037 in [0.94 mm]
Conductor Type	Solid	
Dielectric	PTFE	0.119 in [3.02 mm]
First Shield	Tinned Copper Braid 100% coverage	0.141 in [3.58 mm]
Jacket	Silver	[]

Environmental Specifications Temperature

Operating Range

-55 to +125 deg C

Configuration:

- Formable Cable
- 1 Shield(s)

Features:

- Dimensionally the same as standard solid outer conductor semirigid coax
- Standard semi-rigid connectors can be used
- Cable is hand formable and does not require special tools to bend
- Connectors are easily soldered to Tin soaked outer conductor
- Cable can be formed more than once without damage to outer conductor
- High RF Shielding >100 dB

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Compliance Certifications (see product page for current document)

D	lotte	d ar	hr	Oth	۵r	Dat	ta

Notes:

.141 Semi-rigid Formable Coax Cable Jacket from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: .141 Semi-rigid Formable Coax Cable Jacket FM-SR141TB-BULK

URL: https://www.fairviewmicrowave.com/invalid-alias-formable-coax-cable-fm-sr141tb-bulk-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





