

FM82P5010 DATA SHEET

Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz and SMA

Fairview Microwave FM82P5010 is a phase shifter that has phase adjustment range of 180 degrees per GHz with precision rotary dial design for controllable phase adjustment across a frequency range from 0 to 4GHz. With SMA female connectors, this RF phase shifter design is tried and true technology that offers exceptional RF performance characteristics that include 2 dB maximum insertion loss and a maximum VSWR of 1.5:1. Phase shifters are part of Pasternack's comprehensive RF passive product offerings which are available in stock and ready for same-day shipment.

Electrical Specifications (Values at +25° C, Sea Level)

Description	Min	Тур	Max	Units
Frequency Range	DC		4	GHz
Impedance		50		Ohms
Phase Shift	0		720	Degrees
Phase Adjustment	0		180	Deg/GHz
Input VSWR			1.5:1	
Output VSWR				
Insertion Loss			2	dB
Input Power, CW			100	Watts
Input Power, Peak			5	kWatts

5µs pulse, 1% duty cycle

Mechanical Specifications

Size

Length
Width/Diameter
Height
Weight
Body Material and Plating

Configuration

Input Connector
Output Connector

14.65 in [372.11 mm] 2.99 in [75.95 mm] 1.2 in [30.48 mm] 5.3 lbs [2.4 kg] Aluminum

SMA Female SMA Female

Environmental Specifications

Temperature

Operating Range -10 to 50 deg C Storage Range -40 to 70 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Features:

- Phase Tuning Range:0 to 720 degrees
- Rotary Dial Design for Continuous Adjustment
- Frequency Range from DC to 4GHz
- SMA Female Connectorized Design
- Max VSWR 1.5:1
- Max Power Rating: 100 Watts (CW)
- Insertion Loss: 2 dB Max

Applications:

- Test & Measurements
- Radar Development
- Military Communications Systems
- Phase Array Antenna System
- Satellite Communications

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (9

Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com





Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz and SMA from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: Adjustable Phase Shifter, DC to 4GHz, With an Adjustable Phase of 180 Deg. Per GHz and SMA FM82P5010

URL: https://www.fairviewmicrowave.com/sma-adjustable-phase-shifter-dc-4-ghz-fm82p5010-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





