

40 dB WRD-650 Double Ridge Waveguide Loop Coupler, SMA Female Coupled Port, 6.5 GHz to 18 GHz in Aluminum

The FMWRD650CP03-40 is a WRD-650 Directional Loop double ridge waveguide coupler with SMA female coupled port that operates in the frequency range of 6.5 to 18 GHz. This Waveguide component has a maximum VSWR of 1.8:1. These designs are made of painted aluminum and incorporate a Loop configuration that result in a mid-band nominal coupling value of 10, 20, 30, 40 or 50 dB. Common applications for this component would be where power measurements are required within a system for measuring/sampling power or frequency monitoring with minimal signal loss to the main transmission line. Fairview Microwave offers a complete family of waveguide Crossguide, Loop and Broadwall couplers that are in-stock and ship same day.

Electrical Specifications

Description	Min	Typ	Max	Units
Frequency Range	6.5		18	GHz
Impedance		50		Ohms
Coupler				
Nominal Coupling Level		40		dB
Directivity	10			dB
Insertion Loss			0.3	dB
Main Line VSWR			1.15:1	
Secondary Line VSWR			1.8:1	
Coupling Flatness			±2.5	dB
Input Power (CW)			400	Watts
Input Power Peak			3	kWatts

Mechanical Specifications

Size	
Length	3.94 in [100.08 mm]
Width	1.38 in [35.05 mm]
Height	1.38 in [35.05 mm]
Weight	0.29 lbs [131.54 g]

Interface


Waveguide Size	WRD-650
Flange Type	Cover
RF Connector Type	SMA Female
Coupler Body Material and Plating	Aluminum, Gray

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:



Features:

- Three Port Loop Waveguide Coupler
- 40±2.5 dB Nominal Coupling Level
- Integrated SMA Female Connector coupled port
- 6.5 GHz to 18 GHz Frequency Range
- Main Line VSWR < 1.15:1
- Max Power 400W (CW)

Applications:

- Test Benches
- Radar
- Satellite
- Microwave Radio
- Attenuation Measurements
- Power Measurements
- Source Leveling

Fairview Microwave
301 Leora Ln., Suite 100
Lewisville, TX 75056
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com

40 dB WRD-650 Double Ridge Waveguide Loop Coupler, SMA Female Coupled Port, 6.5 GHz to 18 GHz in Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [40 dB WRD-650 Double Ridge Waveguide Loop Coupler, SMA Female Coupled Port, 6.5 GHz to 18 GHz in Aluminum FMWRD650CP03-40](https://www.fairviewmicrowave.com/40db-wrd650-waveguide-broadwall-coupler-18ghz-fmwr650cp03-40-p.aspx)

URL: <https://www.fairviewmicrowave.com/40db-wrd650-waveguide-broadwall-coupler-18ghz-fmwr650cp03-40-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.



