

# FMC1515240 DATA SHEET

# 7/16 DIN Male to 7/16 DIN Male Cable LMR-240 Coax

The 7/16 DIN male to 7/16 DIN male cable using LMR-240 coax, part number FMC1515240, from Fairview Microwave is in-stock and ships same day. This Fairview 7/16 DIN to 7/16 DIN cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The FMC1515240 7/16 DIN male to 7/16 DIN male cable assembly operates to 1.5 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

#### **Electrical Specifications**

Description		Min	Т	ур Мах		Units	
Frequency Range		DC			1.5		GHz
Velocity of Propagation			8	34			%
RF Shielding		90					dB
Capacitance			24.2	[79.4]		pF/f	t [pF/m]
Inductance			0.06 [0.2]		uH/f	uH/ft [uH/m]	
DC Resistance Inner Cor	nductor		3.2 [10.5]		<u>Ω/100</u> 0ft [Ω/Km]		
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]			

#### **Mechanical Specifications**

## **Cable Assembly**

Length*	
Weight	

#### Cable

Cable Type Impedance Inner Conductor Type Inner Conductor Material and Plating Dielectric Type Number of Shields Shield Layer 1 Shield Layer 2 Jacket Material Jacket Diameter 0 in [0 mm] 0.37566 lbs [170.4 g]

LMR-240 50 Ohms Solid Copper PE (F) 1 Tinned Copper Aluminum Tape PE, Black 0.24 in [6.1 mm]



# **Configuration:**

- 7/16 DIN Male
- 7/16 DIN Male
- LMR-240

### **Features:**

- Max Frequency 1.5 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- PE Jacket

# **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com Fairview Microwave

an INFINIT<sup>©</sup> brand



#### Connectors

Description	Connector 1	Connector 2		
Туре	7/16 DIN Male	7/16 DIN Male		
Impedance	50 Ohms	50 Ohms		
Contact Material & Plating	Brass, Silver	Brass, Silver		
Dielectric Type	PTFE	PTFE		
Body Material & Plating	Brass, Tri-Metal	Brass, Tri-Metal		

Environmental Specifi Temperature Operating Range		40 to +85 deg C		
Compliance Certificati	ons (see product pag	ge for current documer	nt)	
Plotted and Other Dat Notes:	а			
How to Order				
Part Number Configura	tion:	FMC1515240 -	xx uu	
				cm = Centimeters <blank> = Inches</blank>
				Length
	40-12 = 12 inches long 40-100cm = 100 cm lo	0		

7/16 DIN Male to 7/16 DIN Male Cable LMR-240 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: 7/16 DIN Male to 7/16 DIN Male Cable LMR-240 Coax FMC1515240


URL: https://www.fairviewmicrowave.com/7-16-male-7-16-male-cable-times-Imr-240-coax-fmc1515240-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







FAIRVIEW MICROWAVE INC.	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].					
TITLE 7/16 DIN Male to 7/16 DIN Male Cable LMR-240 Coax	DWG NO FMC1515240-XX			CAGE CODE 3FKR5		
	CAD FILE 103114	SHEET	SCAL	E N/A	SIZE A	5568

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689