

## FMCA2771-200CM DATA SHEET

# TNC Female to TNC Female Cable in 200 CM Length Using RG223 Coax

The TNC female to TNC female cable using RG223 coax, part number FMCA2771-200CM, from Fairview Microwave is in-stock and ships same day. This Fairview TNC to TNC cable assembly has a female to female gender configuration with 50 ohm flexible RG223 coax. Fairview Microwave's flexible RF cable assemblies are ideal for applications where tight bends and continual flexure are required. The double shielding of this Fairview cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other RF cable assembly value added services including connector orientation or clocking, heat shrink booting and labeling are also available. RF testing can also be performed to document the electrical performance of your cable assembly.

## **Electrical Specifications**

Description	Min	Тур	Max	Un	its
Velocity of Propagation		66		%	6
Capacitance		30.8 [101	.05]	pF/ft [	pF/m]

#### **Mechanical Specifications**

**Cable Assembly** 

 Length\*
 78.74 in [200 cm]

 Weight
 0.2655 lbs [120.43 g]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
PE
RG223
S0 Ohms
Solid
Copper, Silver
PE

Number of Shields
Shield Layer 1
Shield Layer 2
Silver Plated Copper Braid
Silver Plated Copper Braid
PVC, Black

Jacket MaterialPVC, BlackJacket Diameter0.21 in [5.33 mm]

One Time Minimum Bend Radius 1 in [25.4 mm]

#### **Connectors**

Connector 1	Connector 2	
TNC Female	TNC Female	
50 Ohms	50 Ohms	
Brass, Nickel	Brass, Nickel	
	TNC Female 50 Ohms	



## **Configuration:**

- TNC Female
- TNC Female
- RG223

## Features:

- 66% Phase Velocity
- Double Shielded
- PVC Jacket

## **Applications:**

- General Purpose
- Laboratory Use

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:

· Values at 25°C, sea level.

## **How to Order**



TNC Female to TNC Female Cable in 200 CM Length Using RG223 Coax from Fairview Microwave has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99% availability and are part of the broadest selection in the industry.

Click the following link to obtain additional part information: TNC Female to TNC Female Cable in 200 CM Length Using RG223 Coax FMCA2771-200CM

URL: https://www.fairviewmicrowave.com/tnc-female-to-tnc-female-cable-rg223-coax-in-200-cm-and-rohs-fmca2771-200cm-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





