

2.92mm Male Connector Solder Attachment for FMBC001, FMBC002 Cable Low Loss 047 Semi-Rigid

2.92mm male connector with solder attachment for FMBC001 and FMBC002, part number FMCN1506, from Fairview Microwave is in-stock and ships same day.

Fairview's 2.92mm male connector FMCN1506 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Description	Min	Тур	Max	Units
VSWR			1.14:1	
DWV (AC)			500	Vrms
High Potential Voltage			325	Vrms
Corona Discharge			125	Vrms
Insulation Resistance	5,000			MOhms
RF Leakage	-90			dB

Performance by Frequency

Description	F1	F2	F3	F4	F5	Units
Freq. Range	DC to 18	18 to 26.5	26.5 to 45			GHz
VSWR, Max	1.1:1	1.12:1	1.14:1			

Electrical Specification Notes: Insertion Loss = 0.04*SQRT(Fghz) dB

Mechanical Specifications

Size	
Length	0.54 in [13.72 mm]
Width/Dia.	0.35 in [8.89 mm]
Weight	0.01 lbs [4.54 g]
Mating Cycles Mating Torque	500 Cycles 8 to 10 in-lbs [0.90 to 1.13 Nm]

Material Specifications

Description	Material	Plating
Contact	Beryllium Copper	Gold ASTM-B488
Insulation	PTFE	
Body	Beryllium Copper	Gold ASTM-B488

FMCN1506 DATA SHEET



Configuration:

- 2.92mm Male Connector
- 50 Ohms
- Straight Body Geometry
- FMBC001, FMBC002 Interface Type
- Solder Attachment

Features:

- Excellent VSWR of 1.14:1
- Gold Plated Beryllium Copper Contact
- Contact plating according to ASTM-B488

Applications:

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com **Fairview Microwave** an INFINIT[®] brand



 Coupling Nut
 Steel

 Gasket
 Silicone Rubber


Environmental Specifications

Temperature	
Operating Range	-65 to +165 deg C
Shock	MIL-STD-202, Method 213, Condition I
Vibration	MIL-STD-202, Method 204, Condition D
Thermal Shock	MIL-STD-202, Method 107, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:







Assembly Instruction



2.92mm Male Connector Solder Attachment for FMBC001, FMBC002 Cable Low Loss 047 Semi-Rigid from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: 2.92mm Male Connector Solder Attachment for FMBC001, FMBC002 Cable Low Loss 047 Semi-Rigid FMCN1506


URL: https://www.fairviewmicrowave.com/2.92mm-male-fmbc001-fmbc002-connector-fmcn1506-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689







TITLE 2.92mm Male Connector Solder Attachment for FMBC001, FMBC002 Cable Low Loss 047 Semi-Rigid

.х

3. DIMENSIONS ARE IN INCHES [mm].								
DWG NO	FMCN	1506			CAGE C		FKR5	
CAD FILE	01/11/19	SHEET	1 OF 1	SCALE N/A		SIZE A	CN2379	

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689