Fairview Microwave an INFINITE brand

## QMA Male Right Angle Connector Crimp/Solder Attachment for RG58, RG141, RG303, LMR-195, 0.195 inch

RA QMA male connector with crimp/solder attachment for RG58, RG141, RG303, LMR-195 and .195 inch, part number FMCN1894, from Fairview Microwave is instock and ships same day. This QMA male connector operates up to a maximum frequency of 18 GHz. Its right angle body geometry facilitates connections in tight spaces.

Fairview's RA QMA male connector FMCN1894 datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

#### **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz

#### **Mechanical Specifications**

Size Lenath Width/Dia. Height Weight

	-		
Description	Materi	al Plating	
Material Specification	ns		
Weight		0.022 lbs [9.98 g]	
Height		0.73 in [18.54 mm]	
man bia.			

Contact	Brass	Gold
Insulation	PTFE	
Outer Conductor	Phosphor Bronze	Tri-Metal
Body	Brass	Tri-Metal

#### **Environmental Specifications**

Temperature **Operating Range** 

-65 to +165 deg C

0.89 in [22.61 mm]

0.38 in [9.65 mm]

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



**FMCN1894** 

DATA SHEET

## **Configuration:**

- QMA Male Connector
- 50 Ohms
- Right Angle Body Geometry
- RG58, RG141, RG303, LMR-195, .195 inch Interface Type
- Crimp/Solder Attachment

### **Features:**

- Operating Frequency of 18 GHz Max.
- Gold Plated Brass Contact

## **Applications:**

- General Purpose Test
- Custom Cable Assemblies

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com






QMA Male Right Angle Connector Crimp/Solder Attachment for RG58, RG141, RG303, LMR-195, 0.195 inch from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: QMA Male Right Angle Connector Crimp/Solder Attachment for RG58, RG141, RG303, LMR-195, 0.195 inch FMCN1894


URL: https://www.fairviewmicrowave.com/qma-male-rg58-rg141-rg303-Imr-195-.195-connector-fmcn1894-p.aspx



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689



# FMCN1894 DATA SHEET



301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689