

# SM4237 DATA SHEET

## SMA Female to N Female Bulkhead Adapter

SMA female to type N female bulkhead adapter part number SM4237 from Fairview Microwave is in-stock and ships same day. This Fairview SMA to type N adapter has a female to female gender configuration. SM4237 SMA female to type N female adapter operates to 18 GHz. The SMA connector mates mechanically with commercially available 3.5mm and 2.92mm (K) connectors. Our RF SMA to type N bulkhead adapter allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The Fairview Microwave RF adapter provides excellent VSWR of 1.2:1 maximum.

RF adapters can be used to enable connections between two connector types that would otherwise not mate. Certain RF adapter configurations can also be used to protect connectors on expensive equipment where the number of connect and disconnect cycles is high. An RF, microwave, or millimeter wave adapter is connected to the equipment and the commonly changed connection is made with the adapter which can be easily replaced when it wears out after high usage; such adapters are referred to as connector savers. Fairview Microwave also offers bulkhead, panel mount, hermetically sealed, reverse polarity, and isolated ground adapter varieties to serve all of your RF, microwave and millimeter wave needs.

## **Electrical Specifications**

Description	Min	Тур	Max	Units
Frequency Range	DC		18	GHz
VSWR			1.2:1	

**Electrical Specification Notes:** 

Values at 25°C, sea level.

### **Mechanical Specifications**

Size
Length
Width
Weight

1.235 in [31.37 mm] 0.81 in [20.57 mm] 0.0836 lbs [37.92 g]

Description	Connector 1	Connector 2	
Туре	SMA Female	N Female	
Polarity	Standard	Standard	
Mating Cycles	500	500	

### **Material Specifications**

Description	Connector 1	Connector 2		
Туре	SMA Female	N Female		
Contact Material	Beryllium Copper	Beryllium Copper		
Contact Plating	Gold over Nickel	Gold over Nickel		
Contact Plating Spec.	MIL-G-45204	MIL-G-45204		
Insulation Material	PTFE	PTFE		
Outer Contact Material	Passivated Stainless Steel	Passivated Stainless Steel		
Outer Contact Plating Spec.	ASTM A380	ASTM-A380		



## **Configuration:**

- SMA Female Connector 1
- N Female Connector 2
- 50 Ohms
- Straight Body Geometry
- Bulkhead Mount Method

### **Features:**

- VSWR of 1.2:1 max up to 18 GHz
- Contact plating according to MIL-G-45204
- Gold over Nickel Plated Beryllium Copper Contact

## **Applications:**

- Enables Between Series Connections
- General Purpose Test
- · Rack Mounted Equipment

Fairview Microwave 1130 Junction Dr. #100 Allen, TX 75013

Tel: 1-800-715-4396 / (972) 649-6678

Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





### **Environmental Specifications**

**Temperature** 


Operating Range Vibration Salt Spray -55 to +100 deg C MIL-STD 202, Method 204, Condition D (20 G's) MIL-STD 202, Method 101, Condition B, 5% salt solution

**Compliance Certifications** (see product page for current document)

### **Plotted and Other Data**

Notes:

**Typical Performance Data** 



SMA Female to N Female Bulkhead Adapter from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: SMA Female to N Female Bulkhead Adapter SM4237

URL: https://www.fairviewmicrowave.com/sma-female-n-female-bulkhead-adapter-sm4237-p.aspx


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

1130 Junction Dr. #100 Allen, TX 75013 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689

Copyright © 2016 REV 1.1 Page 2 of 3







FAIRVIEW MICROWAVE INC.  ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM	NOTES:  1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.  3. DIMENSIONS ARE IN INCHES [mm].					
SMA Female to N Female Bulkhead Adapter	DWG NO SM4237		(	CAGE CODE 3FKR5		
	CAD FILE 110415	SHEET	SCALE	N/A	SIZE A	150