



# Type N F/F In/Out Coaxial RF Surge Protector, 800MHz - 2.5GHz, DC Pass, 300W, IP67, 20kA, Hybrid, Bracket Toward Body

RF surge protector (also known as lightning arrester) FMSP1010 from Fairview Microwave, utilizing a patented hybrid protection technology integrating a silicon avalanche suppression diode (SASD) and a MOV and gas tube, enables a quick response to a lightning surge to protect critical hardware while maintaining the RF performance. This RF surge protector component is manufactured in a coaxial inline design with wide operating frequency range. All Fairview Microwave RF surge protector products are available in stock with same day shipping.

<b>Electrical</b>	<b>Specifi</b>	ications
-------------------	----------------	----------

Surge Protector Type		Hybrid		
DC Handling		DC Pass		
Description	Min	Тур	Max	Units
Frequency Range	0.8		2.5	GHz
Impedance		50		Ohms
VSWR			1.1:1	
Return Loss			26	dB
Insertion Loss			0.1	dB
Input Power, CW			300	Watts
Surge Current IEC 61000-4-5 8/20µs	Waveform		20	kA
Turn On Voltage		6.5		Volts
Throughput Energy FOR 3kA @ 8/20µs WA	VEFORM		175	uJ

## **Mechanical Specifications**

Weight 0.581 lbs [263.54 g]

Configuration

Input Connector N Female Output Connector N Female

**Environmental Specifications Temperature** 

Operating Range -50 to 85 deg C

Ingress Protection (IP) Rating IP 67

**Compliance Certifications** (see product page for current document)

#### **Plotted and Other Data**

Notes:



#### Features:

- · Surge current of 20kA
- Max Power 300W
- Frequency range from 800 MHz to 2.5GHz
- N-type female connectors
- Waterproof IP67 rated
- DC Pass
- VSWR < 1.1:1
- · Low insertion loss
- · CE & RoHS compliant

# Applications:

- GPS systems
- Active antenna systems

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com






Type N F/F In/Out Coaxial RF Surge Protector, 800MHz - 2.5GHz, DC Pass, 300W, IP67, 20kA, Hybrid, Bracket Toward Body from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: Type N F/F In/Out Coaxial RF Surge Protector, 800MHz - 2.5GHz, DC Pass, 300W, IP67, 20kA, Hybrid, Bracket Toward Body FMSP1010

URL: https://www.fairviewmicrowave.com/type-n-surge-protector-2.5ghz-hybrid-fmsp1010-p.aspx









STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

\*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

#### NOTES:

HARDWARE INCLUDED.

### **REGULATORY COMPLIANCE:**

CE2011/65/EU(RoHS DIRECTIVE)

