

**WR-137 Waveguide Section 3 Inch Length Straight
Using UG-344/U Flange With a 5.85 GHz to 8.2 GHz
Frequency Range in Commercial Grade**

Electrical Specifications*

Description	Min	Typ	Max	Units
Frequency Range	5.85		8.2	GHz
VSWR			1.03:1	
Insertion Loss			0.1 [0.33]	dB/ft [dB/m]

* Values at 25°C, sea level

Mechanical Specifications

Waveguide Size
Waveguide Design
Section Length

WR-137
Commercial Grade
3 in [76.2 mm]

Flange 1

Interface
Material
Plating

UG-344/U
Copper Alloy
Paint

Waveguide

Interface
Material
Plating

WR-137
Copper Alloy
Paint

Flange 2

Interface
Material
Plating

UG-344/U
Copper Alloy
Paint

Compliance Certifications (visit www.FairviewMicrowave.com for current document)

Plotted and Other Data

Notes:

- Values at 25 °C, sea level



Fairview Microwave
1130 Junction Dr. #100
Allen, TX 75013
Tel: 1-800-715-4396 / (972) 649-6678
Fax: (972) 649-6689
www.fairviewmicrowave.com
sales@fairviewmicrowave.com


WR-137 Waveguide Section 3 Inch Length Straight Using UG-344/U Flange With a 5.85 GHz to 8.2 GHz Frequency Range in Commercial Grade from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [WR-137 Waveguide Section 3 Inch Length Straight Using UG-344/U Flange With a 5.85 GHz to 8.2 GHz Frequency Range in Commercial Grade SMF137S-03](http://www.fairviewmicrowave.com/wr-137-waveguide-section-ug-344-flange-5.85-8.2-ghz-smf137s-03-p.aspx)

URL: <http://www.fairviewmicrowave.com/wr-137-waveguide-section-ug-344-flange-5.85-8.2-ghz-smf137s-03-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.





FAIRVIEW MICROWAVE INC. ALLEN, TX 75013 WWW.FAIRVIEWMICROWAVE.COM		NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].			
TITLE WR-137 Waveguide Section 3 Inch Length Straight Using UG-344/U Flange With a 5.85 GHz to 8.2 GHz Frequency Range in Commercial Grade		DWG NO SMF137S		CAGE CODE 3FKR5	
CAD FILE	062414	SHEET	SCALE	N/A	SIZE A 2233