an INFINITe brand



DATA SHEET

RA 7/16 DIN Male Low PIM Connector Solder Attachment for SPP-250-LLPL Cable

Times Microwave Systems Connector Specification

RA 7/16 DIN male connector with solder/solder attachment for Times' SPP-250-LLPL, part number TC-SPP250-716M-RA-LP, from Times Microwave offered by Fairview Microwave is in-stock and ships same day. This 7/16 DIN male connector operates up to a maximum frequency of 6 GHz and offers good VSWR of 1.3:1. The 7/16 DIN male connector also has low passive intermodulation (PIM) of -160 dBc. Its right angle body geometry facilitates connections in tight spaces.

Times Microwave's RA 7/16 DIN male connector TC-SPP250-716M-RA-LP datasheet specifications and outline drawing are shown in this PDF below. Our extensive offering of RF, microwave and millimeter wave connectors allows designers to configure and customize their signal connections however they like. From providing an I/O for a board design to creating a custom cable assembly configuration, Fairview Microwave has a connector solution to meet your needs. Fairview Microwave also has the expertise to build your custom cable assemblies for you and ship them same-day.

Electrical Specifications

Min	Тур	Max	Units	
DC		6	GHz	
		1.3:1		
		0.1	dB	
		-160	dBc	
		1,500	Vdc	
е		0.4	mOhms	
е		1.5	mOhms	
5,000			MOhms	
	DC DC	DC DC	DC 6 1.3:1 0.1 -160 1,500 e 0.4 e 1.5	

Mechanical Specifications

Size

Lenath 1.31 in [33.27 mm] Width/Dia. 1.14 in [28.96 mm] Height 1.02 in [25.91 mm]

Mating Torque 265.52 in-lbs [30.00 Nm]

Material Specifications

Description	Material	Plating
Contact	Brass	Silver 196 µin
Insulation	PTFE	
Body	Brass	Nickel 118 µin
Coupling Nut	Brass	Nickel 118 µin



Configuration:

- 7/16 DIN Male Connector
- 50 Ohms
- Right Angle Body Geometry
- SPP-250-LLPL Interface Type
- Solder/Solder Attachment
- Low PIM Design

Features:

- Operating Frequency of 6 GHz Max.
- Good VSWR of 1.3:1
- PIM levels better than -160 dBc
- Silver Plated Brass Contact
- 196 µin contact plating

Applications:

- General Purpose Test
- Wireless Communications
- Custom Cable Assemblies
- Low PIM Applications
- Distributed Antenna Systems (DAS)

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689

www.fairviewmicrowave.com sales@fairviewmicrowave.com Gasket Silicone Rubber

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Humidity IP6

Shock MIL-STD 202G, Method 213, Condition I
Vibration MIL-STD 202G, Method 204, Condition B
Thermal Shock MIL-STD 202G, Method 107, Condition B

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

RA 7/16 DIN Male Low PIM Connector Solder Attachment for SPP-250-LLPL Cable from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Allen, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: RA 7/16 DIN Male Low PIM Connector Solder Attachment for SPP-250-LLPL Cable TC-SPP250-716M-RA-LP

URL: https://www.fairviewmicrowave.com/7-16-din-male-spp-250-llpl-connector-tc-spp250-716m-ra-lp-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume any liability arising out of the use of any part or documentation.

301 Leora Ln., Suite 100, Lewisville, TX 75056 | Tel: 1-800-715-4396 / (972) 649-6678 / Fax: (972) 649-6689





Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
RA 7/16 DIN Male Low PIM Connector Solder Attachment for SPP-250-LLPL Cable	TC-SPP250-716M-RA-LP			CAGE CODE 3FKR5			
	CAD FILE 04/17/19	SHEET 1 OF 1	SCALE	E N/A	SIZE A	7361	