

FMWCA1076 DATA SHEET

WR-187 to SMA Female Waveguide to Coax Adapter UDR48 with 3.94 GHz to 5.99 GHz C Band in Aluminum

The FMWCA1076 is a waveguide to coaxial adapter operating in the C Band with a 3.94 to 5.99 GHz frequency range. This adapter offers a WR-187 waveguide interface size coupled with a precision tolerance UDR48 flange. The FMWCA1076 is constructed of aluminum and painted to ensure durability. The coaxial connector offered by this adapter uses a SMA Female connector.

Configuration

Waveguide Size WR-187
Flange UDR48
RF Connector SMA Female
Impedance 50 Ohms
Body Geometry Right Angle

Electrical Specifications

Description	Min	Тур	Max	Units
Frequency Range	3.94		5.99	GHz
VSWR			1.25:1	
Input Power (CW)			50	Watts

Mechanical Specifications

Size

 Length
 2.64 in [67.06 mm]

 Width
 3.54 in [89.92 mm]

 Height
 2.5 in [63.5 mm]

 Weight
 0.375 lbs [170.1 g]

RF Connector

Connector Type SMA Female
Body Material and Plating Stainless Steel

Waveguide Interface

Waveguide Type WR-187
Flange Type UDR48
Body Material and Plating Aluminum

Environmental Specifications

Temperature

Operating Range -40 to +70 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

• Values at +25 °C, sea level unless stated otherwise



Features:

- C band
- 3.94 to 5.99 GHz Frequency Range
- WR-187 Waveguide Interface
- UDR48 Flange
- SMA Female RF Interface
- Comprehensive waveguide offerings also include E-Bends, H-Bends, Sections, Filters, Terminations, Couplers, and more.

Fairview Microwave 301 Leora Ln., Suite 100 Lewisville, TX 75056 Tel: 1-800-715-4396 / (972) 649-6678 Fax: (972) 649-6689 www.fairviewmicrowave.com sales@fairviewmicrowave.com





WR-187 to SMA Female Waveguide to Coax Adapter UDR48 with 3.94 GHz to 5.99 GHz C Band in Aluminum from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.


For additional information on this product, please click the following link: WR-187 to SMA Female Waveguide to Coax Adapter UDR48 with 3.94 GHz to 5.99 GHz C Band in Aluminum FMWCA1076


URL: https://www.fairviewmicrowave.com/wr187-sma-female-waveguide-coax-adapter-udr48-fmwca1076-p.aspx
















STANDARD TOLERANCES

.X ±0.2 .XX ±0.01 .XXX ±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

Fairview Microwave	NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].						
an INFINIT® brand							
WR-187 to SMA Female Waveguide to Coax Adapter UDR48 with 3.94 GHz to 5.99 GHz C Band in Aluminum	DWG NO FMWCA1076			CAGE CODE 3FKR5			
	CAD FILE 07/03/19	SHEET 1 OF 1	SCAL	E N/A	SIZE A	7361	